

Australian Declaration of Conformity

The undersigned, representing the following
Manufacturer

Allen-Bradley Company, Inc.
6400 W. Enterprise Drive
Mequon, Wisconsin 53092
USA

Supplier Code Number (SCN): N223

and the RA Authorised Supplier within Australia

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic. 3130
Australia

Australian Company Number (ACN): 005 549 477

herewith declare that the Products
Product identification (brand and
catalogue number/part number):

Adjustable Frequency AC Drives
Allen-Bradley Bulletin 160/160S (Series C) and Accessories
(reference the attached list of catalogue numbers)

are in conformity with the following:

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

AS/NZS 2064, 1997, Group 1, Class A Limits and Methods of Measurement of electronic disturbance
characteristic of industrial, scientific, and medical (ISM) radio frequency
equipment

Detailed Technical Information is maintained at:

Allen-Bradley Company, Inc
6400 W. Enterprise Drive
Mequon, Wisconsin 53092
USA

Compliance Folder is maintained at:

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic 3130
Australia


Document No.: AU-DST-0019-B-EN

Document No.: AUS-0040-B

Manufacturer:

Authorised Person within Australia:

Signature



Name: Daniel Stewart
Position: Manager, Product Certification
Engineering
Date: 27-Oct-2000

Signature



Name: William Grant Roberts
Position: Managing Director
Date: 3-Nov-2000

| <i>Catalogue number</i> | <i>Series¹</i> | <i>Description</i> |
|-------------------------|---------------------------|--|
| 160S-AA02NSF1 | C | AC Drive, 0.5 Hp, 200-240V., 1 Phase |
| 160S-AA02NPS1 | C | AC Drive, 0.5 Hp, 200-240V., 1 Phase |
| 160S-AA03NSF1 | C | AC Drive, 0.75 Hp, 200-240V., 1 Phase |
| 160S-AA03NPS1 | C | AC Drive, 0.75 Hp, 200-240V., 1 Phase |
| 160S-AA04NSF1 | C | AC Drive, 1 Hp, 200-240V., 1 Phase |
| 160S-AA04NPS1 | C | AC Drive, 1 Hp, 200-240V., 1 Phase |
| 160S-AA08NSF1 | C | AC Drive, 2 Hp, 200-240V., 1 Phase |
| 160S-AA08NPS1 | C | AC Drive, 2 Hp, 200-240V., 1 Phase |
| 160-AA02NSF1 | C | AC Drive, 0.5 Hp, 200-240V., 3 Phase |
| 160-AA02NPS1 | C | AC Drive, 0.5 Hp, 200-240V., 3 Phase |
| 160-AA03NSF1 | C | AC Drive, 0.75 Hp, 200-240V., 3 Phase |
| 160-AA03NPS1 | C | AC Drive, 0.75 Hp, 200-240V., 3 Phase |
| 160-AA04NSF1 | C | AC Drive, 1 Hp, 200-240V., 3 Phase |
| 160-AA04NPS1 | C | AC Drive, 1 Hp, 200-240V., 3 Phase |
| 160-AA08NSF1 | C | AC Drive, 2 Hp, 200-240V., 3 Phase |
| 160-AA08NPS1 | C | AC Drive, 2 Hp, 200-240V., 3 Phase |
| 160-AA12NSF1 | C | AC Drive, 3 Hp, 200-240V., 3 Phase |
| 160-AA12NPS1 | C | AC Drive, 3 Hp, 200-240V., 3 Phase |
| 160-AA18NSF1 | C | AC Drive, 5 Hp, 200-240V., 3 Phase |
| 160-AA18NPS1 | C | AC Drive, 5 Hp, 200-240V., 3 Phase |
| 160-BA01NSF1 | C | AC Drive, 0.5 Hp, 380-460V., 3 Phase |
| 160-BA01NPS1 | C | AC Drive, 0.5 Hp, 380-460V., 3 Phase |
| 160-BA02NSF1 | C | AC Drive, 0.75 Hp, 380-460V., 3 Phase |
| 160-BA02NPS1 | C | AC Drive, 0.75 Hp, 380-460V., 3 Phase |
| 160-BA03NSF1 | C | AC Drive, 1 Hp, 380-460V., 3 Phase |
| 160-BA03NPS1 | C | AC Drive, 1 Hp, 380-460V., 3 Phase |
| 160-BA04NSF1 | C | AC Drive, 2 Hp, 380-460V., 3 Phase |
| 160-BA04NPS1 | C | AC Drive, 2 Hp, 380-460V., 3 Phase |
| 160-BA06NSF1 | C | AC Drive, 3 Hp, 380-460V., 3 Phase |
| 160-BA06NPS1 | C | AC Drive, 3 Hp, 380-460V., 3 Phase |
| 160-BA10NSF1 | C | AC Drive, 5 Hp, 380-460V., 3 Phase |
| 160-BA10NPS1 | C | AC Drive, 5 Hp, 380-460V., 3 Phase |
| 160-AA04NP03 | C | AC Drive, 2 Hp, 200-240V., 3 Phase, Def. Purpose |
| 160-AA08NP03 | C | AC Drive, 3 Hp, 200-240V., 3 Phase, Def. Purpose |
| 160-AA12NP03 | C | AC Drive, 5 Hp, 200-240V., 3 Phase, Def. Purpose |
| 160-AA18NP03 | C | AC Drive, 7.5 Hp, 200-240V., 3 Phase, Def. Purpose |
| 160-BA03NP03 | C | AC Drive, 2 Hp, 380-460V., 3 Phase, Def. Purpose |
| 160-BA04NP03 | C | AC Drive, 3 Hp, 380-460V., 3 Phase, Def. Purpose |
| 160-BA06NP03 | C | AC Drive, 5 Hp, 380-460V., 3 Phase, Def. Purpose |
| 160-BA10NP03 | C | AC Drive, 7.5 Hp, 380-460V., 3 Phase, Def. Purpose |
| 160S-AA02PSF1 | C | AC Drive, 0.5 Hp, 200-240V., 1 Phase |
| 160S-AA02PPS1 | C | AC Drive, 0.5 Hp, 200-240V., 1 Phase |
| 160S-AA03PSF1 | C | AC Drive, 0.75 Hp, 200-240V., 1 Phase |
| 160S-AA03PPS1 | C | AC Drive, 0.75 Hp, 200-240V., 1 Phase |
| 160S-AA04PSF1 | C | AC Drive, 1 Hp, 200-240V., 1 Phase |
| 160S-AA04PPS1 | C | AC Drive, 1 Hp, 200-240V., 1 Phase |
| 160S-AA08PSF1 | C | AC Drive, 2 Hp, 200-240V., 1 Phase |
| 160S-AA08PPS1 | C | AC Drive, 2 Hp, 200-240V., 1 Phase |
| 160-AA02PSF1 | C | AC Drive, 0.5 Hp, 200-240V., 3 Phase |
| 160-AA02PPS1 | C | AC Drive, 0.5 Hp, 200-240V., 3 Phase |

| <i>Catalogue number</i> | <i>Series ¹</i> | <i>Description</i> |
|-------------------------|----------------------------|--|
| 160-AA03PSF1 | C | AC Drive, 0.75 Hp, 200-240V., 3 Phase |
| 160-AA03PPS1 | C | AC Drive, 0.75 Hp, 200-240V., 3 Phase |
| 160-AA04PSF1 | C | AC Drive, 1 Hp, 200-240V., 3 Phase |
| 160-AA04PPS1 | C | AC Drive, 1 Hp, 200-240V., 3 Phase |
| 160-AA08PSF1 | C | AC Drive, 2 Hp, 200-240V., 3 Phase |
| 160-AA08PPS1 | C | AC Drive, 2 Hp, 200-240V., 3 Phase |
| 160-AA12PSF1 | C | AC Drive, 3 Hp, 200-240V., 3 Phase |
| 160-AA12PPS1 | C | AC Drive, 3 Hp, 200-240V., 3 Phase |
| 160-AA18PSF1 | C | AC Drive, 5 Hp, 200-240V., 3 Phase |
| 160-AA18PPS1 | C | AC Drive, 5 Hp, 200-240V., 3 Phase |
| 160-BA01PSF1 | C | AC Drive, 0.5 Hp, 380-460V., 3 Phase |
| 160-BA01PPS1 | C | AC Drive, 0.5 Hp, 380-460V., 3 Phase |
| 160-BA02PSF1 | C | AC Drive, 0.75 Hp, 380-460V., 3 Phase |
| 160-BA02PPS1 | C | AC Drive, 0.75 Hp, 380-460V., 3 Phase |
| 160-BA03PSF1 | C | AC Drive, 1 Hp, 380-460V., 3 Phase |
| 160-BA03PPS1 | C | AC Drive, 1 Hp, 380-460V., 3 Phase |
| 160-BA04PSF1 | C | AC Drive, 2 Hp, 380-460V., 3 Phase |
| 160-BA04PPS1 | C | AC Drive, 2 Hp, 380-460V., 3 Phase |
| 160-BA06PSF1 | C | AC Drive, 3 Hp, 380-460V., 3 Phase |
| 160-BA06PPS1 | C | AC Drive, 3 Hp, 380-460V., 3 Phase |
| 160-BA10PSF1 | C | AC Drive, 5 Hp, 380-460V., 3 Phase |
| 160-BA10PPS1 | C | AC Drive, 5 Hp, 380-460V., 3 Phase |
| 160S-AA02RSF1 | C | AC Drive, 0.5 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA02RPS1 | C | AC Drive, 0.5 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA03RSF1 | C | AC Drive, 0.75 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA03RPS1 | C | AC Drive, 0.75 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA04RSF1 | C | AC Drive, 1 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA04RPS1 | C | AC Drive, 1 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA08RSF1 | C | AC Drive, 2 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160S-AA08RPS1 | C | AC Drive, 2 Hp, 200-240V., 1 Phase, Replacement Drive |
| 160-AA02RSF1 | C | AC Drive, 0.5 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA02RPS1 | C | AC Drive, 0.5 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA03RSF1 | C | AC Drive, 0.75 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA03RPS1 | C | AC Drive, 0.75 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA04RSF1 | C | AC Drive, 1 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA04RPS1 | C | AC Drive, 1 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA08RSF1 | C | AC Drive, 2 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA08RPS1 | C | AC Drive, 2 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA12RSF1 | C | AC Drive, 3 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA12RPS1 | C | AC Drive, 3 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA18RSF1 | C | AC Drive, 5 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-AA18RPS1 | C | AC Drive, 5 Hp, 200-240V., 3 Phase, Replacement Drive |
| 160-BA01RSF1 | C | AC Drive, 0.5 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA01RPS1 | C | AC Drive, 0.5 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA02RSF1 | C | AC Drive, 0.75 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA02RPS1 | C | AC Drive, 0.75 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA03RSF1 | C | AC Drive, 1 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA03RPS1 | C | AC Drive, 1 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA04RSF1 | C | AC Drive, 2 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA04RPS1 | C | AC Drive, 2 Hp, 380-460V., 3 Phase, Replacement Drive |

| <i>Catalogue number</i> | <i>Series ¹</i> | <i>Description</i> |
|-------------------------|----------------------------|--|
| 160-BA06RSF1 | C | AC Drive, 3 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA06RPS1 | C | AC Drive, 3 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA10RSF1 | C | AC Drive, 5 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA10RPS1 | C | AC Drive, 5 Hp, 380-460V., 3 Phase, Replacement Drive |
| 160-BA06LSF1 | C | AC Drive, 3.6 A, 380-460V., 3 Phase, Def. Purpose |
| 160-BA06LPS1 | C | AC Drive, 3.6 A, 380-460V., 3 Phase, Def. Purpose |
| 160-AA12LSF1 | C | AC Drive, 5.9 A, 200-240V., 3 Phase, Def. Purpose |
| 160-AA12LPS1 | C | AC Drive, 5.9 A, 200-240V., 3 Phase, Def. Purpose |
| 160-NX3 | C | AC Drive, 3.0 A, 200-240V., 3 Phase, Def. Purpose |
| 160S-RFA-16-B | A | Line Filter, 2 Hp, 200-240V., 1 Phase |
| 160-CMA1 | A | Capacitor Module, 0.5-5Hp, 200-240V. |
| 160-CMB1 | A | Capacitor Module, 0.5-5Hp, 200-240V. |
| 160-BMA1 | A | Dynamic Brake Mod., 0.5-1Hp,200-240V. |
| 160-BMA2 | A | Dynamic Brake Mod., 2Hp,200-240V |
| 160-BMB1 | A | Dynamic Brake Mod., 0.5-1Hp,380-460V |
| 160-BMB2 | A | Dynamic Brake Mod., 2-5Hp,380-460V |
| 160-DN2 | A | DeviceNet Module |
| 160S-LFA1 | A | Line Filter, 0.5-2Hp, 200-240V., 1 Phase |
| 160-LFA1 | A | Line Filter, 0.5-2Hp, 200-240V., 3 Phase |
| 160-LFA2 | A | Line Filter, 3Hp, 200-240V., 3Phases |
| 160-LFB1 | A | Line Filter, 0.5-3Hp, 380-460V., 3 Phase |
| 160-RFB-3A | A | Line Filter, 0.5-0.75Hp, 200-240V, 3Phase, 0.5-1Hp, 380-460V, 3Phase |
| 160-RFA-6A | A | Line Filter, 0.5-0.75Hp, 200-240V, 1Phase |
| 160S-RFA-9A | C | Line Filter, 0.5-1Hp, 200-240V., 1Phase |
| 160S-RFA-10-A | A | Line Filter, 0.5-.75Hp, 200-240V., 1Phase |
| 160S-RFA-16-A | A | Line Filter, 2Hp, 200-240V., 1 Phase |
| 160-RS1 | A | RS-232 Communication Module |
| 160-P1 | A | Program Keypad Module |
| 160-P2 | C | Remote Keypad |
| 160-P3 | C | Copycat Keypad |
| 160-RPA | C | Remote Programming Adaptor |
| 160-DM-SF1 | B | Interface Module, 24V. dc, analog |
| 160-DM-PS1 | B | Interface Module, 24V. dc, preset |
| 160-RFB-5-A | C | Line Filter, 0.5-1Hp, 200-240V, 3 Phase, 0.5-2Hp, 380-460V, 3 Phase |
| 160-RFB-14-A | C | Line Filter, 2-3Hp, 200-240V, 3 Phase, 3Hp, 380-460V, 3 Phase |
| 160-RFB-14-B | C | Line Filter, 5Hp, 380-460V, 3 Phase |
| 160-RFB-22-B | C | Line Filter, 5Hp, 200-240V, 3 Phase |

1) If no series number is given, then all series are covered