

Australian Declaration of Conformity

The undersigned, representing the following
Manufacturer

and the RA Authorised Supplier within Australia

Allen-Bradley Company, Inc.
1201 South 2nd Street
Milwaukee, WI 53204
USA

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic. 3130
Australia

Supplier Code Number (SCN): N223

Australian Company Number (ACN): 005 549 477

herewith declare that the Products **“Flex I/O” Product Family**
Product identification (brand and **Allen-Bradley 1794 Series**
catalogue number/part number): (reference the attached list of catalogue numbers)

are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation, and in an enclosure that will provide additional 10dB attenuation:

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

AS/NZS CISPR 11:2002, Group 1, Limits and Methods of Measurement of electronic disturbance characteristic
Class A of industrial, scientific, and medical (ISM) radio frequency equipment

Detailed Technical Information is maintained at:

Allen-Bradley Company, Inc.
1 Allen-Bradley Drive
Mayfield Heights, Ohio 44124-6118
USA

Compliance Folder is maintained at:

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic 3130
Australia

Document No.: 1005

Document No.: AUS-0031-P

Manufacturer:

Authorised Person within Australia:



Signature

Signature

Name: John R. Mowry
Position: Compliance Engineer
Date: 4-Feb-2008

Name: Donald Timothy Werner
Position: Managing Director
Date: 5-Feb-2008

<i>Catalogue Number</i>	<i>Series ¹</i>	<i>Description</i>
1203-FB1	B	Scanport Terminal Base
1203-FM1	B	Scanport
1794-ACN		ControlNet Communication Adapter
1794-ACN15		ControlNet Communication Adapter, Phase 1.5+
1794-ACN15K		ControlNet Communication Adapter (conformal coated)
1794-ACNR		Redundant ControlNet Communication Adapter
1794-ACNR15		Redundant ControlNet Communication Adapter, Phase 1.5+
1794-ACNR15K		Redundant ControlNet Communication Adapter (conformal coated)
1794-ADN		DeviceNet Communication Adapter
1794-ADNK		DeviceNet Communication Adapter (conformal coated)
1794-AENT		10/100Mb Ethernet Communication Adapter
1794-APB	B	Profibus Communication Adapter
1794-ASB	B	RIO Communication Adapter
1794-ASB2		Dual Channel RIO Communication Adapter
1794-ASBK	B	RIO Communication Adapter (conformal coated)
1794-ASBLT		RIO Classic Communication Adapter
1794-FLA		FlexLogix Extended Local FlexBus Adapter
1794-HSC		High Speed Counter Module
1794-IA16		16 channel, 85-132Vac, Input Module
1794-IA8		8 channel, 85-132Vac, Input Module
1794-IA8K		8 channel, 85-132Vac, Input Module (conformal coated)
1794-IA8I		8 channel, Isolated, 85-132Vac, Input Module
1794-IB10XOB6		10 Input/6 Output, 24Vdc, Combo Module
1794-IB16		16 channel, 24Vdc, Sink Input Module
1794-IB16D		16 channel, 24Vdc, Diagnostic Sink Input Module
1794-IB16K		16 channel, 24Vdc, Sink Input Module (conformal coated)
1794-IB16XOB16P		16 Input/16 Output, 24Vdc, Combo Module
1794-IB32		32 channel, 24Vdc, Sink Input Module
1794-IB8		8 channel, 24Vdc, Sink Input Module
1794-IB8S		8 channel, 24Vdc, Sensor Input Module
1794-IC16		16 channel, 48Vdc, Sink Input Module
1794-IE12		12 Channel, 24Vdc, Analog Input Module
1794-IE4XOE2	B	4 Input/2 Output, Analog Combo Module
1794-IE8	B	8 Channel, 24Vdc, Analog Input Module
1794-IE8K	B	8 Channel, 24Vdc, Analog Input Module (conformal coated)
1794-IE8XOE4		8 Input/4 Output, Analog Combo Module
1794-IF2XOF2I		2 Input/2 Output, Isolated Analog Combo Module
1794-IF4I		4 Channel Isolated Analog Input Module
1794-IJ2		2 Channel/2 Gate Output Frequency Counter Module
1794-IJ2K		2 Channel/2 Gate Output Frequency Counter Module (conformal coated)
1794-IM8		8 Channel, 220Vac, Input Module
1794-IR8		8 Channel, 24Vdc, RTD Analog Input Module
1794-IRT8		8 Channel, 24Vdc, RTD/Thermocouple Analog Input Module
1794-IRT8K		8 Channel, 24Vdc, RTD/Thermocouple Analog Input Module (conformal coated)
1794-IT8		8 Channel, 24Vdc, Thermocouple Analog Input Module
1794-IV16		16 channel, 24Vdc, Source Input Module
1794-L33		FlexLogix processor (64kB)

¹ Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number</i>	<i>Series ¹</i>	<i>Description</i>
1794-L34		FlexLogix Processor (512kB)
1794-OA16		16 channel, 85-132Vac, Output Module
1794-OA8		8 channel, 85-132Vac, Output Module
1794-OA8K		8 channel, 85-132Vac, Output Module (conformal coated)
1794-OA8I		8 channel, Isolated, 85-132Vac, Output Module
1794-OB16		16 channel, 24Vdc, Source Output Module
1794-OB16D		16 channel, 24Vdc, Diagnostic Source Output Module
1794-OB16P		16 channel, 24Vdc, Limited, Source Output Module
1794-OB16PK		16 channel, 24Vdc, Limited, Source Output Module (conformal coated)
1794-OB32P		32 channel, 24Vdc, Limited, Source Output Module
1794-OB8		8 channel, 24Vdc, Source Output Module
1794-OB8EP		8 channel, 24Vdc, Electronically Fused, Source Output Module
1794-OB8EPK		8 channel, 24Vdc, Electronically Fused, Source Output Module (conformal coated)
1794-OC16		16 channel, 48Vdc, Source Output Module
1794-OE12		12 Channel, 24Vdc, Analog Output Module
1794-OE4	B	4 Channel, 24Vdc, Analog Output Module
1794-OE4K	B	4 Channel, 24Vdc, Analog Output Module (conformal coated)
1794-OF4I		4 Channel Isolated Analog Output Module
1794-OM8		8 Channel, 220Vac, Output Module
1794-OV16		16 channel, 24Vdc, Sink Output Module
1794-OV16P		16 channel, 24Vdc, Limited, Sink Output Module
1794-OW8		8 Channel, 125Vdc/240Vac, Relay Output Module
1794-OW8K		8 Channel, 125Vdc/240Vac, Relay Output Module (conformal coated)
1794-PS1		120/240Vac Input, 24Vdc 1Amp Output, Power Supply
1794-PS13		120/240Vac Input, 24Vdc 1.3Amp Output, Power Supply
1794-PS3		120/240Vac Input, 24Vdc 3Amp Output, Power Supply
1794-TB2		2 Wire Terminal Base
1794-TB3		3 Wire Terminal Base
1794-TB32		32-Point Terminal Base
1794-TB32S		32-Point, Spring Clamp, Terminal Base
1794-TB37DS		37-Point, D-Shell, Terminal Base
1794-TB3G		3 Wire, Cage Clamp, Gnd., Terminal Base
1794-TB3GK		3 Wire, Cage Clamp, Gnd., Terminal Base (conformal coated)
1794-TB3GS		3 Wire, Spring Clamp, Gnd., Terminal Base
1794-TB3K		3 Wire Terminal Base (conformal coated)
1794-TB3S		3 Wire, Spring Clamp, Terminal Base
1794-TB3T		3 Wire, Analog, Terminal Base
1794-TB3TS		3 Wire, Analog, Spring Clamp, Terminal Base
1794-TB62DS		62-Point, D-Shell, Terminal Base
1794-TB62DSG		62-Point, D-Shell, Analog Terminal Base
1794-TB62DST		62-Point, D-Shell, Analog Terminal Base (w/CJC)
1794-TBKD		2 Wire, Knife-Switch, Terminal Base
1794-TBN		NEMA Terminal Base
1794-TBNF		NEMA, Fused, Terminal Base
1794-TBNFK		NEMA, Fused, Terminal Base (conformal coated)
1794-TBNK		NEMA Terminal Base (conformal coated)
1794-VHSC		Very High Speed Counter

¹ Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

¹ Products of the series level shown or higher are certified. If no series number is given, then all series are covered.