

Australian Declaration of Conformity

The undersigned, representing the following
Manufacturer

and the RA Authorised Supplier within Australia

Rockwell Automation, Inc.
6400 West Enterprise Drive
Mequon, WI 53092
USA

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic. 3130
Australia

Supplier Code Number (SCN): N223

Australian Company Number (ACN): 005 549 477

herewith declare that the Products **Adjustable Frequency AC Drives**
Product identification (brand and **Allen-Bradley PowerFlex 700**
catalogue number/part number): (reference the attached list of catalogue numbers)

are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

EN 61800-3: 2004

Adjustable Speed Electrical Power Drive Systems – Part 3: EMC Product
Standard Including Specific Test Methods

Detailed Technical Information is maintained at:

Rockwell Automation, Inc.
6400 West Enterprise Drive
Mequon, WI 53092
USA

Compliance Folder is maintained at:

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic 3130
Australia

Document No.: AU-DST-0038-D-EN

Document No.: AUS-0076-D

Manufacturer:

Authorised Person within Australia:

Signature



Name: Daniel Stewart
Position: Manager, Product Certification
Engineering
Date: 2-July-2007

Signature



Name: Donald Timothy Werner
Position: Managing Director
Date: 28-July-2007

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Adjustable Frequency AC Drives		
20BB2P2A*****		AC Drive, 0.5 Hp, 208/240V, 3 Phase
20BB4P2A*****		AC Drive, 1 Hp, 208/240V, 3 Phase
20BB6P8A*****		AC Drive, 2 Hp, 208/240V, 3 Phase
20BB9P6A*****		AC Drive, 3 Hp, 208/240V, 3 Phase
20BB015A*****		AC Drive, 5 Hp, 208/240V, 3 Phase
20BB022A*****		AC Drive, 7.5 Hp, 208/240V, 3 Phase
20BB028A*****		AC Drive, 10 Hp, 208/240V, 3 Phase
20BB042A*****		AC Drive, 15 Hp, 208/240V, 3 Phase
20BB052A*****		AC Drive, 20 Hp, 208/240V, 3 Phase
20BB070A*****		AC Drive, 25 Hp, 208/240V, 3 Phase
20BB080A*****		AC Drive, 30 Hp, 208/240V, 3 Phase
20BB104x*****		AC Drive, 40 Hp, 208/240V, 3 Phase
20BB130x*****		AC Drive, 50 Hp, 208/240V, 3 Phase
20BB154x*****		AC Drive, 60 Hp, 208/240V, 3 Phase
20BB192x*****		AC Drive, 75 Hp, 208/240V, 3 Phase
20BB260x*****		AC Drive, 100 Hp, 208/240V, 3 Phase
20BG104x*****		AC Drive, 40 Hp, 280/325V, DC Input
20BG130x*****		AC Drive, 50 Hp, 280/325V, DC Input
20BG154x*****		AC Drive, 60 Hp, 280/325V, DC Input
20BG192x*****		AC Drive, 75 Hp, 280/325V, DC Input
20BN104x*****		AC Drive, 40 Hp, 280/325V, DC Input
20BN130x*****		AC Drive, 50 Hp, 280/325V, DC Input
20BN154x*****		AC Drive, 60 Hp, 280/325V, DC Input
20BN192x*****		AC Drive, 75 Hp, 280/325V, DC Input
20BN260x*****		AC Drive, 100 Hp, 280/325V, DC Input
20BC1P3A*****		AC Drive, 0.5 Hp, 400V, 3 Phase
20BC2P1A*****		AC Drive, 1 Hp, 400V, 3 Phase
20BC3P5A*****		AC Drive, 2 Hp, 400V, 3 Phase
20BC5P0A*****		AC Drive, 3 Hp, 400V, 3 Phase
20BC8P7A*****		AC Drive, 5 Hp, 400V, 3 Phase
20BC011A*****		AC Drive, 7.5 Hp, 400V, 3 Phase
20BC015A*****		AC Drive, 10 Hp, 400V, 3 Phase
20BC022A*****		AC Drive, 15 Hp, 400V, 3 Phase
20BC030A*****		AC Drive, 20 Hp, 400V, 3 Phase
20BC037A*****		AC Drive, 25 Hp, 400V, 3 Phase
20BC043A*****		AC Drive, 30 Hp, 400V, 3 Phase
20BC056A*****		AC Drive, 40 Hp, 400V, 3 Phase
20BC072A*****		AC Drive, 50 Hp, 400V, 3 Phase
20BC085A*****		AC Drive, 60 Hp, 400V, 3 Phase
20BC105x*****		AC Drive, 75 Hp, 400V, 3 Phase
20BC125x*****		AC Drive, 100 Hp, 400V, 3 Phase
20BC140x*****		AC Drive, 100 Hp, 400V, 3 Phase
20BC170x*****		AC Drive, 125 Hp, 400V, 3 Phase
20BC205x*****		AC Drive, 150 Hp, 400V, 3 Phase
20BC260x*****		AC Drive, 200 Hp, 400V, 3 Phase

¹ **x** may be **A, F, G** or **N** indicating drive enclosure options, * may be **any number or letter** indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Adjustable Frequency AC Drives		
20BH105x*****		AC Drive, 75 Hp, 540V, DC Input
20BH125x*****		AC Drive, 100 Hp, 540V, DC Input
20BH170x*****		AC Drive, 125 Hp, 540V, DC Input
20BH205x*****		AC Drive, 150 Hp, 540V, DC Input
20BP105x*****		AC Drive, 75 Hp, 540V, DC Input
20BP125x*****		AC Drive, 100 Hp, 540V, DC Input
20BP140x*****		AC Drive, 100 Hp, 540V, DC Input
20BP170x*****		AC Drive, 125 Hp, 540V, DC Input
20BP205x*****		AC Drive, 150 Hp, 540V, DC Input
20BP260x*****		AC Drive, 200 Hp, 540V, DC Input
20BD1P1A*****		AC Drive, 0.5 Hp, 480V, 3 Phase
20BD2P1A*****		AC Drive, 1 Hp, 480V, 3 Phase
20BD3P4A*****		AC Drive, 2 Hp, 480V, 3 Phase
20BD5P0A*****		AC Drive, 3 Hp, 480V, 3 Phase
20BD8P0A*****		AC Drive, 5 Hp, 480V, 3 Phase
20BD011A*****		AC Drive, 7.5 Hp, 480V, 3 Phase
20BD014A*****		AC Drive, 10 Hp, 480V, 3 Phase
20BD022A*****		AC Drive, 15 Hp, 480V, 3 Phase
20BD027A*****		AC Drive, 20 Hp, 480V, 3 Phase
20BD034A*****		AC Drive, 25 Hp, 480V, 3 Phase
20BD040A*****		AC Drive, 30 Hp, 480V, 3 Phase
20BD052A*****		AC Drive, 40 Hp, 480V, 3 Phase
20BD065A*****		AC Drive, 50 Hp, 480V, 3 Phase
20BD077A*****		AC Drive, 60 Hp, 480V, 3 Phase
20BD096x*****		AC Drive, 75 Hp, 480V, 3 Phase
20BD125x*****		AC Drive, 100 Hp, 480V, 3 Phase
20BD135x*****		AC Drive, 100 Hp, 480V, 3 Phase
20BD156x*****		AC Drive, 125 Hp, 480V, 3 Phase
20BD180x*****		AC Drive, 150 Hp, 480V, 3 Phase
20BD248x*****		AC Drive, 200 Hp, 480V, 3 Phase
20BJ096x*****		AC Drive, 75 Hp, 650V, DC Input
20BJ125x*****		AC Drive, 100 Hp, 650V, DC Input
20BJ156x*****		AC Drive, 125 Hp, 650V, DC Input
20BJ180x*****		AC Drive, 150 Hp, 650V, DC Input
20BR096x*****		AC Drive, 75 Hp, 650V, DC Input
20BR125x*****		AC Drive, 100 Hp, 650V, DC Input
20BR156x*****		AC Drive, 125 Hp, 650V, DC Input
20BR180x*****		AC Drive, 150 Hp, 650V, DC Input
20BR248x*****		AC Drive, 200 Hp, 650V, DC Input
20BE077x*****		AC Drive, 75 Hp, 600V, 3 Phase
20BE099x*****		AC Drive, 100 Hp, 600V, 3 Phase
20BE125x*****		AC Drive, 125 Hp, 600V, 3 Phase
20BE144x*****		AC Drive, 150 Hp, 600V, 3 Phase

<i>Catalogue</i>	<i>Series²</i>	<i>Description</i>
------------------	---------------------------	--------------------

¹ **x** may be **A, F, G** or **N** indicating drive enclosure options, * may be **any number or letter** indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Number¹</i>		
Adjustable Frequency AC Drives		
20BK077x*****		<i>AC Drive, 75 Hp, 810V, DC Input</i>
20BK099x*****		<i>AC Drive, 100 Hp, 810V, DC Input</i>
20BK125x*****		<i>AC Drive, 125 Hp, 810V, DC Input</i>
20BK144x*****		<i>AC Drive, 150 Hp, 810V, DC Input</i>
20BT077x*****		<i>AC Drive, 75 Hp, 810V, DC Input</i>
20BT099x*****		<i>AC Drive, 100 Hp, 810V, DC Input</i>
20BT125x*****		<i>AC Drive, 125 Hp, 810V, DC Input</i>
20BT144x*****		<i>AC Drive, 150 Hp, 810V, DC Input</i>
20BF052x*****		<i>AC Drive, 50 Hp, 690V, 3 Phase</i>
20BF060x*****		<i>AC Drive, 60 Hp, 690V, 3 Phase</i>
20BF082x*****		<i>AC Drive, 75 Hp, 690V, 3 Phase</i>
20BF098x*****		<i>AC Drive, 100 Hp, 690V, 3 Phase</i>
20BF119x*****		<i>AC Drive, 125 Hp, 690V, 3 Phase</i>
20BF142x*****		<i>AC Drive, 150 Hp, 690V, 3 Phase</i>
20BM077x*****		<i>AC Drive, 75 Hp, 932V, DC Input</i>
20BM099x*****		<i>AC Drive, 100 Hp, 932V, DC Input</i>
20BM125x*****		<i>AC Drive, 125 Hp, 932V, DC Input</i>
20BM144x*****		<i>AC Drive, 150 Hp, 932V, DC Input</i>
20BW077x*****		<i>AC Drive, 75 Hp, 932V, DC Input</i>
20BW099x*****		<i>AC Drive, 100 Hp, 932V, DC Input</i>
20BW125x*****		<i>AC Drive, 125 Hp, 932V, DC Input</i>
20BW144x*****		<i>AC Drive, 150 Hp, 932V, DC Input</i>
Drive Interface Modules		
20-HIM-A1		<i>Digital LED Drive Interface Module</i>
20-HIM-A2		<i>Digital LCD Drive Interface Module</i>
20-HIM-A3		<i>Full Numeric LCD Drive Interface Module</i>
20-HIM-A4		<i>Analog LCD Drive Interface Module</i>
20-HIM-A5		<i>Programmer Only LCD Drive Interface Module</i>
20-HIM-C3		<i>Panel Mount Full Numeric LCD Drive Module (IP66)</i>
20-HIM-C5		<i>Panel Mount Programmer Only LCD Drive Module (IP66)</i>
20-HIM-C3S		<i>Panel Mount Full Numeric LCD Drive Module (IP66)</i>
20-HIM-C5S		<i>Panel Mount Programmer Only LCD Drive Module (IP66)</i>

¹ **x** may be **A, F, G** or **N** indicating drive enclosure options, * may be **any number or letter** indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Drive Communication Modules		
20-COMM-D		<i>DeviceNet Comm Module</i>
20-COMM-R		<i>Remote I/O Comm Module</i>
20-COMM-S		<i>RS-485 Serial Comm Module</i>
20-COMM-H		<i>RS-485 Serial Comm Module (HVAC)</i>
20-COMM-C		<i>ControlNet Comm Module</i>
20-COMM-E		<i>Ethernet Comm Module</i>
20-COMM-M		<i>Modbus / TCP Comm Module</i>
20-COMM-Q		<i>Fiber Optic Comm Module</i>
20-XCOMM-DC-BASE		<i>DBI Comm Adaptors</i>
20-XCOMM-IO-OPT1		<i>Digital I/O</i>
1203-SSS		<i>Serial to Scanport Converter</i>

¹ **x** may be **A, F, G** or **N** indicating drive enclosure options, * may be **any number or letter** indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.