

**Australian Declaration of Conformity**

The undersigned, representing the following  
Manufacturer

and the RA Authorised Supplier within Australia

**Rockwell Automation, Inc.**  
6400 West Enterprise Drive  
Mequon, WI 53092  
USA

**Rockwell Automation Australia Ltd.**  
37 Chapman Street (PO Box 190)  
Blackburn, Vic. 3130  
Australia

**Supplier Code Number (SCN): N223**

**Australian Company Number (ACN): 005 549 477**

herewith declare that the Products  
Product identification (brand and  
catalogue number/part number):

**Adjustable Frequency AC Drives**  
**Allen-Bradley PowerFlex 700H**  
(reference the attached list of catalogue numbers)

are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

EN 61800-3: 2004

Adjustable speed electrical power drive systems – Part 3: EMC  
requirements and specific test methods

Detailed Technical Information is maintained at:

Rockwell Automation, Inc.  
6400 West Enterprise Drive  
Mequon, WI 53092  
USA

Compliance Folder is maintained at:

Rockwell Automation Australia Ltd.  
37 Chapman Street (PO Box 190)  
Blackburn, Vic 3130  
Australia

Document No.: AU-DST-0083-B-EN

Document No.: AUS-0136-B

Manufacturer:

Authorised Person within Australia:

Signature



Name: Daniel Stewart  
Position: Manager, Product Certification  
Engineering  
Date: 28-Dec-2007

Signature



Name: Donald Timothy Werner  
Position: Managing Director  
Date: 15-Jan-2008

<i>Catalogue Number<sup>1</sup></i>	<i>Series<sup>2</sup></i>	<i>Description</i>
Adjustable Frequency AC Drives		
20CC261x*		AC Drive, 132kW, 400V, 3 Phase
20CC300x*		AC Drive, 160kW, 400V, 3 Phase
20CC385x*		AC Drive, 200kW, 400V, 3 Phase
20CC460x*		AC Drive, 250kW, 400V, 3 Phase
20CC500x*		AC Drive, 250kW, 400V, 3 Phase
20CC590x*		AC Drive, 315kW, 400V, 3 Phase
20CC650x*		AC Drive, 355kW, 400V, 3 Phase
20CC730x*		AC Drive, 400kW, 400V, 3 Phase
20CC820x*		AC Drive, 450 kW, 400V, 3 Phase
20CC920x*		AC Drive, 500 kW, 400V, 3 Phase
20CC1K0x*		AC Drive, 560 kW, 400V, 3 Phase
20CC1K1x*		AC Drive, 630 kW, 400V, 3 Phase
20CC1K3x*		AC Drive, 710 kW, 400V, 3 Phase
20CC1K4x*		AC Drive, 800 kW, 400V, 3 Phase
20CC1K7x*		AC Drive, 1000kW, 400V, 3 Phase
20CC2K1x*		AC Drive, 1200kW, 400V, 3 Phase
20CC2K7x*		AC Drive, 1600kW, 400V, 3 Phase
20CH261x*		AC Drive, 132kW, 540V, DC Input
20CH300x*		AC Drive, 160kW, 540V, DC Input
20CH385x*		AC Drive, 200kW, 540V, DC Input
20CH460x*		AC Drive, 250kW, 540V, DC Input
20CH500x*		AC Drive, 250kW, 540V, DC Input
20CH590x*		AC Drive, 315kW, 540V, DC Input
20CH650x*		AC Drive, 355kW, 540V, DC Input
20CH730x*		AC Drive, 400kW, 540V, DC Input
20CH820x*		AC Drive, 450 kW, 540V, DC Input
20CH920x*		AC Drive, 500 kW, 540V, DC Input
20CH1K0x*		AC Drive, 560 kW, 540V, DC Input
20CH1K1x*		AC Drive, 630 kW, 540V, DC Input
20CH1K3x*		AC Drive, 710 kW, 540V, DC Input
20CH1K4x*		AC Drive, 800 kW, 540V, DC Input
20CH1K7x*		AC Drive, 1000kW, 540V, DC input
20CH2K1x*		AC Drive, 1200kW, 540V, DC input
20CH2K7x*		AC Drive, 1600kW, 540V, DC input
20CD261x*		AC Drive, 200 Hp, 480V, 3 Phase
20CD300x*		AC Drive, 250 Hp, 480V, 3 Phase
20CD385x*		AC Drive, 300 Hp, 480V, 3 Phase
20CD460x*		AC Drive, 350 Hp, 480V, 3 Phase
20CD500x*		AC Drive, 450 Hp, 480V, 3 Phase
20CD590x*		AC Drive, 500 Hp, 480V, 3 Phase
20CD650x*		AC Drive, 500 Hp, 480V, 3 Phase
20CD730x*		AC Drive, 600 Hp, 480V, 3 Phase
20CD820x*		AC Drive, 700 Hp, 480V, 3 Phase
20CD920x*		AC Drive, 800 Hp, 480V, 3 Phase
20CD1K0x*		AC Drive, 900 Hp, 480V, 3 Phase
20CD1K1x*		AC Drive, 1000 Hp, 480V, 3 Phase

<sup>1</sup> x may be A or N indicating drive enclosure options, \* may be **any number or letter** indicating drive options which do not impact this DoC.

<sup>2</sup> Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number<sup>1</sup></i>	<i>Series<sup>2</sup></i>	<i>Description</i>
Adjustable Frequency AC Drives		
20CD1K3x*		AC Drive, 1200 Hp, 480V, 3 Phase
20CD1K4x*		AC Drive, 1250 Hp, 480V, 3 Phase
20CD1K7x*		AC Drive, 1400HP, 480V, 3 Phase
20CD2K1x*		AC Drive, 1700HP, 480V, 3 Phase
20CD2K7x*		AC Drive, 2000HP, 480V, 3 Phase
20CJ261x*		AC Drive, 200 Hp, 650V, DC Input
20CJ300x*		AC Drive, 250 Hp, 650V, DC Input
20CJ385x*		AC Drive, 300 Hp, 650V, DC Input
20CJ460x*		AC Drive, 350 Hp, 650V, DC Input
20CJ500x*		AC Drive, 450 Hp, 650V, DC Input
20CJ590x*		AC Drive, 500 Hp, 650V, DC Input
20CJ650x*		AC Drive, 500 Hp, 650V, DC Input
20CJ730x*		AC Drive, 600 Hp, 650V, DC Input
20CJ820x*		AC Drive, 700 Hp, 650V, DC Input
20CJ920x*		AC Drive, 800 Hp, 650V, DC Input
20CJ1K0x*		AC Drive, 900 Hp, 650V, DC Input
20CJ1K1x*		AC Drive, 1000 Hp, 650V, DC Input
20CJ1K3x*		AC Drive, 1200 Hp, 650V, DC Input
20CJ1K4x*		AC Drive, 1250 Hp, 650V, DC Input
20CJ1K7x*		AC Drive, 1400HP, 650V, DC Input
20CJ2K1x*		AC Drive, 1700HP, 650V, DC Input
20CJ2K7x*		AC Drive, 2000HP, 650V, DC Input
20CE170x*		AC Drive, 150 Hp, 600V, 3 Phase
20CE208x*		AC Drive, 200 Hp, 600V, 3 Phase
20CE261x*		AC Drive, 250 Hp, 600V, 3 Phase
20CE325x*		AC Drive, 350 Hp, 600V, 3 Phase
20CE385x*		AC Drive, 400 Hp, 600V, 3 Phase
20CE416x*		AC Drive, 450 Hp, 600V, 3 Phase
20CE460x*		AC Drive, 500 Hp, 600V, 3 Phase
20CE502x*		AC Drive, 500 Hp, 600V, 3 Phase
20CE590x*		AC Drive, 600 Hp, 600V, 3 Phase
20CE650x*		AC Drive, 700 Hp, 600V, 3 Phase
20CE750x*		AC Drive, 800 Hp, 600V, 3 Phase
20CE820x*		AC Drive, 900 Hp, 600V, 3 Phase
20CE920x*		AC Drive, 900 Hp, 600V, 3 Phase
20CE1K0x*		AC Drive, 1000 Hp, 600V, 3 Phase
20CE1K1x*		AC Drive, 1100 Hp, 600V, 3 Phase
20CE1K5x*		AC Drive, 1400HP, 600V, 3 Phase
20CE1K9x*		AC Drive, 1600HP, 600V, 3 Phase
20CE2K2x*		AC Drive, 2000HP, 600V, 3 Phase
20CK170x*		AC Drive, 150 Hp, 810V, DC Input
20CK208x*		AC Drive, 200 Hp, 810V, DC Input
20CK261x*		AC Drive, 250 Hp, 810V, DC Input
20CK325x*		AC Drive, 350 Hp, 810V, DC Input

<i>Catalogue</i>	<i>Series<sup>2</sup></i>	<i>Description</i>
------------------	---------------------------	--------------------

<sup>1</sup> x may be A or N indicating drive enclosure options, \* may be **any number or letter** indicating drive options which do not impact this DoC.

<sup>2</sup> Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Number<sup>1</sup></i>		
Adjustable Frequency AC Drives		
20CK385x*		AC Drive, 400 Hp, 810V, DC Input
20CK416x*		AC Drive, 450 Hp, 810V, DC Input
20CK460x*		AC Drive, 500 Hp, 810V, DC Input
20CK502x*		AC Drive, 500 Hp, 810V, DC Input
20CK590x*		AC Drive, 600 Hp, 810V, DC Input
20CK650x*		AC Drive, 700 Hp, 810V, DC Input
20CK750x*		AC Drive, 800 Hp, 810V, DC Input
20CK820x*		AC Drive, 900 Hp, 810V, DC Input
20CK920x*		AC Drive, 900 Hp, 810V, DC Input
20CK1K0x*		AC Drive, 1000 Hp, 810V, DC Input
20CK1K1x*		AC Drive, 1100 Hp, 810V, DC Input
20CK1K5x*		AC Drive, 1400HP, 810V, DC Input
20CK1K9x*		AC Drive, 1600HP, 810V, DC Input
20CK2K2x*		AC Drive, 2000HP, 810V, DC Input
20CF170x*		AC Drive, 160 kW, 690V, 3 Phase
20CF208x*		AC Drive, 200 kW, 690V, 3 Phase
20CF261x*		AC Drive, 250 kW, 690V, 3 Phase
20CF325x*		AC Drive, 315 kW, 690V, 3 Phase
20CF385x*		AC Drive, 355 kW, 690V, 3 Phase
20CF416x*		AC Drive, 400 kW, 690V, 3 Phase
20CF460x*		AC Drive, 450 kW, 690V, 3 Phase
20CF502x*		AC Drive, 500 kW, 690V, 3 Phase
20CF590x*		AC Drive, 560 kW, 690V, 3 Phase
20CF650x*		AC Drive, 630 kW, 690V, 3 Phase
20CF750x*		AC Drive, 710 kW, 690V, 3 Phase
20CF820x*		AC Drive, 800 kW, 690V, 3 Phase
20CF920x*		AC Drive, 900 kW, 690V, 3 Phase
20CF1K0x*		AC Drive, 1000 kW, 690V, 3 Phase
20CF1K1x*		AC Drive, 1150 kW, 690V, 3 Phase
20CF1K5x*		AC Drive, 1500kW, 690V, 3 Phase
20CF1K9x*		AC Drive, 1800kW, 690V, 3 Phase
20CF2K2x*		AC Drive, 2000kW, 690V, 3 Phase
20CM170x*		AC Drive, 160 kW, 932V, DC Input
20CM208x*		AC Drive, 200 kW, 932V, DC Input
20CM261x*		AC Drive, 250 kW, 932V, DC Input
20CM325x*		AC Drive, 315 kW, 932V, DC Input
20CM385x*		AC Drive, 355 kW, 932V, DC Input
20CM416x*		AC Drive, 400 kW, 932V, DC Input
20CM460x*		AC Drive, 450 kW, 932V, DC Input
20CM502x*		AC Drive, 500 kW, 932V, DC Input
20CM590x*		AC Drive, 560 kW, 932V, DC Input
20CM650x*		AC Drive, 630 kW, 932V, DC Input
20CM750x*		AC Drive, 710 kW, 932V, DC Input
20CM820x*		AC Drive, 800 kW, 932V, DC Input
20CM920x*		AC Drive, 900 kW, 932V, DC Input
20CM1K0x*		AC Drive, 1000 kW, 932V, DC Input

<i>Catalogue</i>	<i>Series<sup>2</sup></i>	<i>Description</i>
------------------	---------------------------	--------------------

<sup>1</sup> x may be A or N indicating drive enclosure options, \* may be any number or letter indicating drive options which do not impact this DoC.

<sup>2</sup> Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Number<sup>1</sup></i>		
Adjustable Frequency AC Drives		
20CM1K1x*		<i>AC Drive, 1150 kW, 932V, DC Input</i>
20CM1K5x*		<i>AC Drive, 1500kW, 932V, DC Input</i>
20CM1K9x*		<i>AC Drive, 1800kW, 932V, DC Input</i>
20CM2K2x*		<i>AC Drive, 2000kW, 932V, DC Input</i>

<sup>1</sup> **x** may be **A** or **N** indicating drive enclosure options, \* may be **any number or letter** indicating drive options which do not impact this DoC.

<sup>2</sup> Products of the series level shown or higher are certified. If no series number is given, then all series are covered.