

Australian Declaration of Conformity

The undersigned, representing the following
Manufacturer

and the RA Authorised Supplier within Australia

Rockwell Automation, Inc.
6400 West Enterprise Drive
Mequon, WI 53092
USA

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic. 3130
Australia

Supplier Code Number (SCN): N223

Australian Company Number (ACN): 005 549 477

herewith declare that the Products
Product identification (brand and
catalogue number/part number):

Adjustable Frequency AC Drives
Allen-Bradley PowerFlex 700S High Power
(reference the attached list of catalogue numbers)

are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

EN 61800-3: 2004

Adjustable speed electrical power drive systems – Part 3: EMC
requirements and specific test methods

Detailed Technical Information is maintained at:

Rockwell Automation, Inc.
6400 West Enterprise Drive
Mequon, WI 53092
USA

Compliance Folder is maintained at:

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic 3130
Australia

Document No.: AU-DST-0084-B-EN

Document No.: AUS-0137-B

Manufacturer:

Authorised Person within Australia:

Signature



Name: Daniel Stewart
Position: Manager, Product Certification
Engineering
Date: 28-Dec-2007

Signature



Name: Donald Timothy Werner
Position: Managing Director
Date: 15-Jan-2008

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Adjustable Frequency AC Drives		
20DC261x*****		AC Drive, 132 kW, 400V, 3 Phase
20DC300x*****		AC Drive, 160 kW, 400V, 3 Phase
20DC385x*****		AC Drive, 200 kW, 400V, 3 Phase
20DC460x*****		AC Drive, 250 kW, 400V, 3 Phase
20DC500x*****		AC Drive, 250 kW, 400V, 3 Phase
20DC590x*****		AC Drive, 315 kW, 400V, 3 Phase
20DC650x*****		AC Drive, 355 kW, 400V, 3 Phase
20DC730x*****		AC Drive, 400 kW, 400V, 3 Phase
20DC820x*****		AC Drive, 450 kW, 400V, 3 Phase
20DC920x*****		AC Drive, 500 kW, 400V, 3 Phase
20DC1K0x*****		AC Drive, 560 kW, 400V, 3 Phase
20DC1K1x*****		AC Drive, 630 kW, 400V, 3 Phase
20DC1K3x*****		AC Drive, 710 kW, 400V, 3 Phase
20DC1K4x*****		AC Drive, 800 kW, 400V, 3 Phase
20DC1K7x*****		AC Drive, 1000kW, 400V, 3 Phase
20DC2K1x*****		AC Drive, 1200kW, 400V, 3 Phase
20DC2K7x*****		AC Drive, 1600kW, 400V, 3 Phase
20DH261x*****		AC Drive, 132 kW, 540V, DC Input
20DH300x*****		AC Drive, 160 kW, 540V, DC Input
20DH385x*****		AC Drive, 200 kW, 540V, DC Input
20DH460x*****		AC Drive, 250 kW, 540V, DC Input
20DH500x*****		AC Drive, 250 kW, 540V, DC Input
20DH590x*****		AC Drive, 315 kW, 540V, DC Input
20DH650x*****		AC Drive, 355 kW, 540V, DC Input
20DH730x*****		AC Drive, 400 kW, 540V, DC Input
20DH820x*****		AC Drive, 450 kW, 540V, DC Input
20DH920x*****		AC Drive, 500 kW, 540V, DC Input
20DH1K0x*****		AC Drive, 560 kW, 540V, DC Input
20DH1K1x*****		AC Drive, 630 kW, 540V, DC Input
20DH1K3x*****		AC Drive, 710 kW, 540V, DC Input
20DH1K4x*****		AC Drive, 800 kW, 540V, DC Input
20DH1K7x*****		AC Drive, 1000kW, 540V, DC input
20DH2K1x*****		AC Drive, 1200kW, 540V, DC input
20DH2K7x*****		AC Drive, 1600kW, 540V, DC input
20DD261x*****		AC Drive, 200 Hp, 480V, 3 Phase
20DD300x*****		AC Drive, 250 Hp, 480V, 3 Phase
20DD385x*****		AC Drive, 300 Hp, 480V, 3 Phase
20DD460x*****		AC Drive, 350 Hp, 480V, 3 Phase
20DD500x*****		AC Drive, 450 Hp, 480V, 3 Phase
20DD590x*****		AC Drive, 500 Hp, 480V, 3 Phase
20DD650x*****		AC Drive, 500 Hp, 480V, 3 Phase
20DD730x*****		AC Drive, 600 Hp, 480V, 3 Phase
20DD820x*****		AC Drive, 700 Hp, 480V, 3 Phase
20DD920x*****		AC Drive, 800 Hp, 480V, 3 Phase
20DD1K0x*****		AC Drive, 900 Hp, 480V, 3 Phase
20DD1K1x*****		AC Drive, 1000 Hp, 480V, 3 Phase

¹ x may be A or N indicating drive enclosure options, * may be any number or letter indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Adjustable Frequency AC Drives		
20DD1K3x*****		AC Drive, 1200 Hp, 480V, 3 Phase
20DD1K4x*****		AC Drive, 1250 Hp, 480V, 3 Phase
20DD1K7x*****		AC Drive, 1400HP, 480V, 3 Phase
20DD2K1x*****		AC Drive, 1700HP, 480V, 3 Phase
20DD2K7x*****		AC Drive, 2000HP, 480V, 3 Phase
20DJ261x*****		AC Drive, 200 Hp, 650V, DC Input
20DJ300x*****		AC Drive, 250 Hp, 650V, DC Input
20DJ385x*****		AC Drive, 300 Hp, 650V, DC Input
20DJ460x*****		AC Drive, 350 Hp, 650V, DC Input
20DJ500x*****		AC Drive, 450 Hp, 650V, DC Input
20DJ590x*****		AC Drive, 500 Hp, 650V, DC Input
20DJ650x*****		AC Drive, 500 Hp, 650V, DC Input
20DJ730x*****		AC Drive, 600 Hp, 650V, DC Input
20DJ820x*****		AC Drive, 700 Hp, 650V, DC Input
20DJ920x*****		AC Drive, 800 Hp, 650V, DC Input
20DJ1K0x*****		AC Drive, 900 Hp, 650V, DC Input
20DJ1K1x*****		AC Drive, 1000 Hp, 650V, DC Input
20DJ1K3x*****		AC Drive, 1200 Hp, 650V, DC Input
20DJ1K4x*****		AC Drive, 1250 Hp, 650V, DC Input
20DJ1K7x*****		AC Drive, 1400HP, 650V, DC Input
20DJ2K1x*****		AC Drive, 1700HP, 650V, DC Input
20DJ2K7x*****		AC Drive, 2000HP, 650V, DC Input
20DE170x*****		AC Drive, 150 Hp, 600V, 3 Phase
20DE208x*****		AC Drive, 200 Hp, 600V, 3 Phase
20DE261x*****		AC Drive, 250 Hp, 600V, 3 Phase
20DE325x*****		AC Drive, 350 Hp, 600V, 3 Phase
20DE385x*****		AC Drive, 400 Hp, 600V, 3 Phase
20DE416x*****		AC Drive, 450 Hp, 600V, 3 Phase
20DE460x*****		AC Drive, 500 Hp, 600V, 3 Phase
20DE502x*****		AC Drive, 500 Hp, 600V, 3 Phase
20DE590x*****		AC Drive, 600 Hp, 600V, 3 Phase
20DE650x*****		AC Drive, 700 Hp, 600V, 3 Phase
20DE750x*****		AC Drive, 800 Hp, 600V, 3 Phase
20DE820x*****		AC Drive, 900 Hp, 600V, 3 Phase
20DE920x*****		AC Drive, 900 Hp, 600V, 3 Phase
20DE1K0x*****		AC Drive, 1000 Hp, 600V, 3 Phase
20DE1K1x*****		AC Drive, 1100 Hp, 600V, 3 Phase
20DE1K5x*****		AC Drive, 1400HP, 600V, 3 Phase
20DE1K9x*****		AC Drive, 1600HP, 600V, 3 Phase
20DE2K2x*****		AC Drive, 2000HP, 600V, 3 Phase
20DK170x*****		AC Drive, 150 Hp, 810V, DC Input
20DK208x*****		AC Drive, 200 Hp, 810V, DC Input
20DK261x*****		AC Drive, 250 Hp, 810V, DC Input
20DK325x*****		AC Drive, 350 Hp, 810V, DC Input
20DK385x*****		AC Drive, 400 Hp, 810V, DC Input
20DK416x*****		AC Drive, 450 Hp, 810V, DC Input

¹ x may be A or N indicating drive enclosure options, * may be any number or letter indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Adjustable Frequency AC Drives		
20DK460x*****		AC Drive, 500 Hp, 810V, DC Input
20DK502x*****		AC Drive, 500 Hp, 810V, DC Input
20DK590x*****		AC Drive, 600 Hp, 810V, DC Input
20DK650x*****		AC Drive, 700 Hp, 810V, DC Input
20DK750x*****		AC Drive, 800 Hp, 810V, DC Input
20DK820x*****		AC Drive, 900 Hp, 810V, DC Input
20DK920x*****		AC Drive, 900 Hp, 810V, DC Input
20DK1K0x*****		AC Drive, 1000 Hp, 810V, DC Input
20DK1K1x*****		AC Drive, 1100 Hp, 810V, DC Input
20DK1K5x*****		AC Drive, 1400HP, 810V, DC Input
20DK1K9x*****		AC Drive, 1600HP, 810V, DC Input
20DK2K2x*****		AC Drive, 2000HP, 810V, DC Input
20DF170x*****		AC Drive, 160 kW, 690V, 3 Phase
20DF208x*****		AC Drive, 200 kW, 690V, 3 Phase
20DF261x*****		AC Drive, 250 kW, 690V, 3 Phase
20DF325x*****		AC Drive, 315 kW, 690V, 3 Phase
20DF385x*****		AC Drive, 355 kW, 690V, 3 Phase
20DF416x*****		AC Drive, 400 kW, 690V, 3 Phase
20DF460x*****		AC Drive, 450 kW, 690V, 3 Phase
20DF502x*****		AC Drive, 500 kW, 690V, 3 Phase
20DF590x*****		AC Drive, 560 kW, 690V, 3 Phase
20DF650x*****		AC Drive, 630 kW, 690V, 3 Phase
20DF750x*****		AC Drive, 710 kW, 690V, 3 Phase
20DF820x*****		AC Drive, 800 kW, 690V, 3 Phase
20DF920x*****		AC Drive, 900 kW, 690V, 3 Phase
20DF1K0x*****		AC Drive, 1000 kW, 690V, 3 Phase
20DF1K1x*****		AC Drive, 1150 kW, 690V, 3 Phase
20DF1K5x*****		AC Drive, 1500kW, 690V, 3 Phase
20DF1K9x*****		AC Drive, 1800kW, 690V, 3 Phase
20DF2K2x*****		AC Drive, 2000kW, 690V, 3 Phase
20DM170x*****		AC Drive, 160 kW, 932V, DC Input
20DM208x*****		AC Drive, 200 kW, 932V, DC Input
20DM261x*****		AC Drive, 250 kW, 932V, DC Input
20DM325x*****		AC Drive, 315 kW, 932V, DC Input
20DM385x*****		AC Drive, 355 kW, 932V, DC Input
20DM416x*****		AC Drive, 400 kW, 932V, DC Input
20DM460x*****		AC Drive, 450 kW, 932V, DC Input
20DM502x*****		AC Drive, 500 kW, 932V, DC Input
20DM590x*****		AC Drive, 560 kW, 932V, DC Input
20DM650x*****		AC Drive, 630 kW, 932V, DC Input
20DM750x*****		AC Drive, 710 kW, 932V, DC Input
20DM820x*****		AC Drive, 800 kW, 932V, DC Input
20DM920x*****		AC Drive, 900 kW, 932V, DC Input
20DM1K0x*****		AC Drive, 1000 kW, 932V, DC Input
20DM1K1x*****		AC Drive, 1150 kW, 932V, DC Input

¹ x may be A or N indicating drive enclosure options, * may be any number or letter indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
Adjustable Frequency AC Drives		
20DM1K5x*****		<i>AC Drive, 1500kW, 932V, DC Input</i>
20DM1K9x*****		<i>AC Drive, 1800kW, 932V, DC Input</i>
20DM2K2x*****		<i>AC Drive, 2000kW, 932V, DC Input</i>

¹ **x** may be **A** or **N** indicating drive enclosure options, * may be **any number or letter** indicating drive options which do not impact this DoC.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.