

EC Declaration of Conformity

The undersigned, representing the following supplier

Rockwell Automation, Inc.
1201 South 2nd Street
Milwaukee, WI 53204
USA

and the authorised representative established within the
Community

Rockwell Automation GmbH
Düsselberger Str. 15
D-42781 Haan, Germany

herewith declare that the Products

**Polymeric Enclosures for Low-Voltage Switchgear and
Controlgear Assemblies**

Product identification (brand and
catalogue number/part number):

Allen-Bradley 598, followed by suffixes
(reference the attached list of catalogue numbers)

are in conformity with the provisions of the following EC Directive(s) when installed in accordance with the
installation instructions contained in the product documentation:

2006/95/EC

Low Voltage Directive

and that the standards and/or technical specifications referenced below have been applied:

EN 60529:1991, including
Amendment A1:2000

Degrees of protection provided by enclosures (IP Code)

EN 50102:1995, including
Amendment A1:1998

Degrees of protection provided by enclosures for electrical equipment against
external mechanical impacts (IK Code)

EN 62208:2003


Empty enclosures for low-voltage switchgear and controlgear assemblies

Year of CE Marking

2005


Supplier:

Authorised Representative in the Community:



Signature

Name: Daniel L. Nachtigall
Position: Supervisor, Standards
Date: 19-Dec-2006



i.V.

Signature

Name: Viktor Schiffer
Position: Engineering Manager
Date: 17-Jan-2007

<i>Catalogue number</i>	<i>Series ¹</i>	<i>Description</i>
598-1PB22G		<i>Polymeric pushbutton enclosure (gray), 1-hole, IP66 (80 x 110 x 70 mm)</i>
598-2PB22G		<i>Polymeric pushbutton enclosure (gray),2-hole, IP66 (80 x 130 x 85 mm)</i>
598-3PB22G		<i>Polymeric pushbutton enclosure (gray), 3-hole, IP66 (80 x 180 x 85 mm)</i>
598-4PB22G		<i>Polymeric pushbutton enclosure (gray), 4-hole, IP66 (80 x 250 x 85 mm)</i>
598-1PB22Y		<i>Polymeric pushbutton enclosure (yellow), 1-hole, IP66 (80 x 110 x 70 mm)</i>
598-2PB22Y		<i>Polymeric pushbutton enclosure (yellow),2-hole, IP66 (80 x 130 x 85 mm)</i>
598-3PB22Y		<i>Polymeric pushbutton enclosure (yellow), 3-hole, IP66 (80 x 180 x 85 mm)</i>
598-4PB22Y		<i>Polymeric pushbutton enclosure (yellow), 4-hole, IP66 (80 x 250 x 85 mm)</i>
598-BS1185		<i>General purpose enclosure (gray), IP66 (280 x 190 x 130 mm)</i>
598-BS332		<i>Polymeric enclosure (gray), screw cover, IP66 (70 x 90 x 52 mm)</i>
598-BS632		<i>Polymeric enclosure (gray), screw cover, IP66 (85 x 165 x 52 mm)</i>
598-BS533		<i>Polymeric enclosure (gray), screw cover, IP66 (80 x 130 x 85 mm)</i>
598-BS733		<i>Polymeric enclosure (gray), screw cover, IP66 (80 x 180 x 85 mm)</i>
598-BS933		<i>Polymeric enclosure (gray), screw cover, IP66 (80 x 250 x 85 mm)</i>
598-BS885		<i>Polymeric enclosure (gray), screw cover, IP66 (190 x 190 x 30 mm)</i>
598-BS1187		<i>Polymeric enclosure (gray), screw cover, IP66 (280 x 190 x 130 mm)</i>
598-BS11115		<i>Polymeric enclosure (gray), screw cover, IP66 (280 x 280 x 130 mm)</i>
598-BS13115		<i>Polymeric enclosure (gray), screw cover, IP66 (340 x 280 x 130 mm)</i>
598-BS1587		<i>Polymeric enclosure (gray), screw cover, IP66 (380 x 190 x 280 mm)</i>
598-BS15117		<i>Polymeric enclosure (gray), screw cover, IP66 (380 x 280 x 180 mm)</i>
598-BS22115		<i>Polymeric enclosure (gray), screw cover, IP66 (560 x 280 x 130 mm)</i>
598-BS22157		<i>Polymeric enclosure (gray), screw cover, IP66 (560 x 380 x 180 mm)</i>
598-BS885C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (190 x 190 x 30 mm)</i>
598-BS1187C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (280 x 190 x 130 mm)</i>
598-BS11115C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (280 x 280 x 130 mm)</i>
598-BS13115C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (340 x 280 x 130 mm)</i>
598-BS1587C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (380 x 190 x 280 mm)</i>
598-BS15117C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (380 x 280 x 180 mm)</i>
598-BS22115C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (560 x 280 x 130 mm)</i>
598-BS22157C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (560 x 380 x 180 mm)</i>
598-DS885M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (190 x 190 x 30 mm)</i>
598-DS1187M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (280 x 190 x 130 mm)</i>
598-DS1587M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (280 x 280 x 130 mm)</i>
598-DS11115M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (340 x 280 x 130 mm)</i>
598-DS13115M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (380 x 190 x 280 mm)</i>
598-DS15117M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (380 x 280 x 180 mm)</i>
598-DS22115M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (560 x 280 x 130 mm)</i>
598-DS22157M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (560 x 380 x 180 mm)</i>
598-DS885CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (190 x 190 x 30 mm)</i>
598-DS1187CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (280 x 190 x 130 mm)</i>
598-DS1587CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (280 x 280 x 130 mm)</i>
598-DS11115CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (340 x 280 x 130 mm)</i>
598-DS13115CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (380 x 190 x 280 mm)</i>
598-DS15117CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (380 x 280 x 180 mm)</i>
598-DS22115CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (560 x 280 x 130 mm)</i>
598-DS22157CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (560 x 380 x 180 mm)</i>

1) If no series number is given, then all series are covered