

Catalogue number	Series ¹	Description
598-1PB22G		<i>Polymeric pushbutton enclosure (gray), 1-hole, IP66 (80 x 110 x 70 mm)</i>
598-2PB22G		<i>Polymeric pushbutton enclosure (gray), 2-hole, IP66 (80 x 130 x 85 mm)</i>
598-3PB22G		<i>Polymeric pushbutton enclosure (gray), 3-hole, IP66 (80 x 180 x 85 mm)</i>
598-4PB22G		<i>Polymeric pushbutton enclosure (gray), 4-hole, IP66 (80 x 250 x 85 mm)</i>
598-1PB22Y		<i>Polymeric pushbutton enclosure (yellow), 1-hole, IP66 (80 x 110 x 70 mm)</i>
598-2PB22Y		<i>Polymeric pushbutton enclosure (yellow), 2-hole, IP66 (80 x 130 x 85 mm)</i>
598-3PB22Y		<i>Polymeric pushbutton enclosure (yellow), 3-hole, IP66 (80 x 180 x 85 mm)</i>
598-4PB22Y		<i>Polymeric pushbutton enclosure (yellow), 4-hole, IP66 (80 x 250 x 85 mm)</i>
598-BS1185		<i>General purpose enclosure (gray), IP66 (280 x 190 x 130 mm)</i>
598-BS332		<i>Polymeric enclosure (gray), screw cover, IP66 (70 x 90 x 52 mm)</i>
598-BS632		<i>Polymeric enclosure (gray), screw cover, IP66 (85 x 165 x 52 mm)</i>
598-BS533		<i>Polymeric enclosure (gray), screw cover, IP66 (80 x 130 x 85 mm)</i>
598-BS733		<i>Polymeric enclosure (gray), screw cover, IP66 (80 x 180 x 85 mm)</i>
598-BS933		<i>Polymeric enclosure (gray), screw cover, IP66 (80 x 250 x 85 mm)</i>
598-BS885		<i>Polymeric enclosure (gray), screw cover, IP66 (190 x 190 x 30 mm)</i>
598-BS1187		<i>Polymeric enclosure (gray), screw cover, IP66 (280 x 190 x 130 mm)</i>
598-BS11115		<i>Polymeric enclosure (gray), screw cover, IP66 (280 x 280 x 130 mm)</i>
598-BS13115		<i>Polymeric enclosure (gray), screw cover, IP66 (340 x 280 x 130 mm)</i>
598-BS1587		<i>Polymeric enclosure (gray), screw cover, IP66 (380 x 190 x 280 mm)</i>
598-BS15117		<i>Polymeric enclosure (gray), screw cover, IP66 (380 x 280 x 180 mm)</i>
598-BS22115		<i>Polymeric enclosure (gray), screw cover, IP66 (560 x 280 x 130 mm)</i>
598-BS22157		<i>Polymeric enclosure (gray), screw cover, IP66 (560 x 380 x 180 mm)</i>
598-BS885C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (190 x 190 x 30 mm)</i>
598-BS1187C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (280 x 190 x 130 mm)</i>
598-BS11115C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (280 x 280 x 130 mm)</i>
598-BS13115C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (340 x 280 x 130 mm)</i>
598-BS1587C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (380 x 190 x 280 mm)</i>
598-BS15117C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (380 x 280 x 180 mm)</i>
598-BS22115C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (560 x 280 x 130 mm)</i>
598-BS22157C		<i>Polymeric enclosure (gray), clear screw cover, IP66 (560 x 380 x 180 mm)</i>
598-DS885M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (190 x 190 x 30 mm)</i>
598-DS1187M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (280 x 190 x 130 mm)</i>
598-DS1587M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (280 x 280 x 130 mm)</i>
598-DS11115M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (340 x 280 x 130 mm)</i>
598-DS13115M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (380 x 190 x 280 mm)</i>
598-DS15117M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (380 x 280 x 180 mm)</i>
598-DS22115M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (560 x 280 x 130 mm)</i>
598-DS22157M		<i>Polymeric enclosure (gray), hinged latch cover, IP66 (560 x 380 x 180 mm)</i>
598-DS885CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (190 x 190 x 30 mm)</i>
598-DS1187CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (280 x 190 x 130 mm)</i>
598-DS1587CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (280 x 280 x 130 mm)</i>
598-DS11115CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (340 x 280 x 130 mm)</i>
598-DS13115CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (380 x 190 x 280 mm)</i>
598-DS15117CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (380 x 280 x 180 mm)</i>
598-DS22115CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (560 x 280 x 130 mm)</i>
598-DS22157CM		<i>Polymeric enclosure (gray), hinged latch clear cover, IP66 (560 x 380 x 180 mm)</i>

1) If no series number is given, then all series are covered