



NEMA 4X/12 SP600 AC Sensorless Vector Drive MODEL NUMBER / LIST PRICE SHEET

**SP600 NEMA 4X/12, IP66 AC Drive
200 - 240 VAC, 50/60 Hz Input: Rating 0.5 to 10 HP**

Catalog Number	Model Number	Stock	Frame	EMC Filter	Horsepower		Drive Amps @ 240 VAC			List
					110% OL	150% OL	Cont.	1 Min.	3 Sec.	
6SP240P5	6SP24X-2P2CTNN	●	B4		0.5	0.33	2.2	2.4	3.3	\$1,060
6SP24001	6SP24X-4P2CTNN	●	B4		1	0.75	4.2	4.8	6.4	\$1,165
6SP24002	6SP24X-6P8CTNN	●	B4		2	1.5	6.8	9	12	\$1,270
6SP24003	6SP24X-9P6CTNN	●	B4		3	2	9.6	10.6	14.4	\$1,395
6SP24005	6SP24X-015CTAN	●	D4	●	5	3	15.3	17.4	23.2	\$1,695
6SP24007	6SP24X-022CTAN	●	D4	●	7.5	5	22	24.2	33	\$2,050
6SP24010	6SP24X-028CTAN	●	D4	●	10	7.5	28	33	44	\$2,820
	6SP24X-2P2CTAN		B4	●	0.5	0.33	2.2	2.4	3.3	\$1,148
	6SP24X-4P2CTAN		B4	●	1	0.75	4.2	4.8	6.4	\$1,253
	6SP24X-6P8CTAN		B4	●	2	1.5	6.8	9	12	\$1,358
	6SP24X-9P6CTAN		B4	●	3	2	9.6	10.6	14.4	\$1,483

**SP600 NEMA 4X/12, IP66 AC Drive
380 - 480 VAC, 50/60 Hz Input: Rating 0.5 to 20 HP**

Catalog Number	Model Number	Stock	Frame	EMC Filter	Horsepower		Drive Amps @ 480 VAC			List
					110% OL	150% OL	Cont.	1 Min.	3 Sec.	
6SP440P5	6SP44X-1P1CTNN	●	B4		0.5	0.33	1.1	1.2	1.6	\$1,415
6SP44001	6SP44X-2P1CTNN	●	B4		1	0.75	2.1	2.4	3.2	\$1,480
6SP44002	6SP44X-3P4CTNN	●	B4		2	1.5	3.4	4.5	6	\$1,665
6SP44003	6SP44X-005CTNN	●	B4		3	2	5	5.5	7.5	\$1,945
6SP44005	6SP44X-008CTNN	●	B4		5	3	8	8.8	12	\$2,225
6SP44007	6SP44X-011CTAN	●	D4	●	7.5	5	11	12.1	16.5	\$2,735
6SP44010	6SP44X-014CTAN	●	D4	●	10	7.5	14	16.5	22	\$2,955
6SP44015	6SP44X-022CTAN	●	D4	●	15	10	22	24.2	33	\$3,795
6SP44020	6SP44X-027CTAN	●	D4	●	20	15	27	33	44	\$4,545
	6SP44X-1P1CTAN		B4	●	0.5	0.33	1.1	1.2	1.6	\$1,503
	6SP44X-2P1CTAN		B4	●	1	0.75	2.1	2.4	3.2	\$1,568
	6SP44X-3P4CTAN		B4	●	2	1.5	3.4	4.5	6	\$1,753
	6SP44X-005CTAN		B4	●	3	2	5	5.5	7.5	\$2,033
	6SP44X-008CTAN		B4	●	5	3	8	8.8	12	\$2,313

Continued on back page

**SP600 NEMA 4X/12, IP66 AC Drive
575 VAC, 50/60 Hz Input: Rating 0.5 to 20 HP**

Catalog Number	Model Number	Stock	Frame	EMC Filter	Horsepower		Drive Amps @ 575 VAC			List
					110% OL	150% OL	Cont.	1 Min.	3 Sec.	
6SP540P5	6SP54X-0P9CTNN	•	B4		0.5	0.33	0.9	1	1.4	\$1,645
6SP54001	6SP54X-1P7CTNN	•	B4		1	0.75	1.7	2	2.6	\$1,665
6SP54002	6SP54X-2P7CTNN	•	B4		2	1.5	2.7	3.6	4.8	\$1,945
6SP54003	6SP54X-3P9CTNN	•	B4		3	2	3.9	4.3	5.8	\$2,235
6SP54005	6SP54X-6P1CTNN	•	B4		5	3	6.1	6.7	9.1	\$2,445
6SP54007	6SP54X-9P0CTNN	•	D4		7.5	5	9	9.9	13.5	\$2,755
6SP54010	6SP54X-011CTNN	•	D4		10	7.5	11	13.5	18	\$3,255
6SP54015	6SP54X-017CTNN	•	D4		15	10	17	18.8	25.5	\$4,035
6SP54020	6SP54X-022CTNN	•	D4		20	15	22	25.5	34	\$4,815

Rockwell Automation
6040 Ponders Court
Greenville, SC 29615
Tel 1.864.297.4800 Fax 1.864.281.2433
[Email adv@powersystems.rockwell.com](mailto:adv@powersystems.rockwell.com)
Web: www.reliance.com www.ptplace.com

RAPS-1035

**Rockwell
Automation**