

ROKLIVE Q2 EXTRA 15% PROMOTION - PRODUCT LIST

Receive 15% extra on orders placed before March 31st, on a wide range of products

- We provide a 15% discount in the form of complimentary products.
- For orders totaling between €10,000 and €100,000 per company.
- For the below listed Product Group Codes (PGCs).
- For all customers at ROKLive EMEA, that order before the end of March 2024.
- For our distributors, the extra benefits will be applied upon sharing the details of the end users.

PGC	PGC Name
17	PF755: 250-400kW, 400V, Frame 8
18	PF755: 350-650HP, 480V, Frame 8
20	PF755: 250-400kW, 690V, Frame 8
21	PF755: 500-850kW, 400V, Frame 9
22	PF755: 700-1250HP, 480V, Frame 9
24	PF755: 500-850kW, 690V, Frame 9
25	PF755: 1000-1250kW, 400V, Frame 10
26	PF755: 1500-1800HP, 480V, Frame 10
28	PF755: 1000-1250kW, 690V, Frame 10
367	7-Class Options and Accessories
402	PF753: 7.5-22KW, 400V, Frames 2,3
403	PF753: 30-55KW, 400V, Frames 4,5
404	PF753: 75-132KW, 400V, Frame 6
412	PF753: 160-250KW, 400V, Frame 7
421	PF753: 10-30HP, 480V, Frames 2,3
424	PF753: 40-75HP, 480V, Frames 4,5
456	PF753: 100-200HP, 480V, Frame 6
457	PF753: 250-350HP, 480V, Frame 7
718	PF755: 7.5-22KW, 400V, Frames 2,3
719	PF755: 30-55KW, 400V, Frames 4,5
720	PF755: 75-132KW, 400V, Frame 6
755	PF755: 160-250KW, 400V, Frame 7
771	PF755: 10-30HP, 480V, Frames 2,3
772	PF755: 40-75HP, 480V, Frames 4,5
773	PF755: 100-200HP, 480V, Frame 6
774	PF755: 250-350HP, 480V, Frame 7
917	SFP
974	Ethernet Appliances
01G	1489-M: Branch Circuit Breakers
02G	1489 Circ. Prot. Accessories
030	SMC-50, Open, Solid State
031	SMC-50, Open, Integral Bypass
03G	1492-SPM: MCB, Supplementary Protectors
03H	1694 Electronic Circuit Protection

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
04G	New Series RCDs, IEC Ground Fault
06F	140G: MCCB External Accessory
06H	Photoelectric Sensors
07F	140G: MCCB Operators
07H	Inductive Sensors with Special Features
083	931S: Signal Conditioners, Standard
08F	140G: MCCB Terminals and Connectors
08H	3D Sensing
090	440R/445L: Light Curtain Controllers
09F	140G: MCCB Internal Accessory
09H	iTRAK 5730
10F	140G: MCCB Comm Accessory
114	193-1EE E100, OL
115	193/592-1EF E100, OL
118	193: E200/PCM, Overload, Low I/O Count Control Modules
11F	140G: MCCB G Frame
120	193: E300, Overload, Sensing, Control, Comms
122	Overload, Mechanical Accessories
126	Overload, Electronic Accessories
128	825-P: Mod Prot Sys, Accessories
12B	SMC-50: Enclosed, Fr E 625-780A
12F	140G: MCCB H Frame
131	809/810: Current Relay, all
135	592: E300, Overload, Sensing, Control, Comms
13F	140G: MCCB I Frame
13H	800Z: Zero-Force Touch Buttons
14F	140G: MCCB J Frame
14G	1492-P: Push -in Clamp Terminal Blocks
157	SMC-3, Open, 108-480A
15F	140G: MCCB K Frame
167	SMC-FLEX, Open, 108-480A
168	SMC-FLEX, Open, 1-85A
169	SMC-FLEX, Open, 625-1250A
16F	140G: MCCB M Frame
16H	1494-400AMP Disconnect & Variable Disc.
17F	140G: MCCB N Frame
17H	800K: Piezo Operators
17J	Class I Div 2 and Specialty Push Buttons
182	Circuit Breakers, North American
183	Circuit Protection Accessories
184	Fuse Holders
185	High Density Protectors
187	Power Blocks
18F	140G: MCCB R Frame
18H	800B: 16mm Operators
18J	Modular and Pre-assembled Tower Lights

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
190	700-FS/FE/FF: DIN Rail Timing Relays
191	700-HA: Tube Base
192	700-HB/HD: Blade Style
193	700-HC: Mini Square Base
197	700-HF: Quick Connect Terminals
198	700-HG/HHF/HJ: Power-Latching Relays
19F	140MG: MCP G Frame
19H	809S/813S/817/819: Machine Alert
19J	141 System Components
200	700-A: Plug-in Accessories
201	700-HN: Sockets and Clips
202	700-S: Solid State Relays
203	700-SH: Hockey Puck and Heatsinks
204	700-HK: Slim Line Relay
205	700-HL: Terminal Block Relays
206	700-HP: Pin Style Terminals
207	1492-W: Legacy Products & Accessories
20H	Solid State Contactors, Single Phase
210	1492-L: Spring Clamp Terminal Blocks
211	DIN Rail
212	DIN Rail Receptacles
215	Markers
216	Printers and Printer Accessories
217	855: Electronic Horns & Square Beacons
219	855: Panel Alarms
21H	Intrinsically Safe Isolators/Converters
220	855: Round Beacons
224	Cables, Wiring Systems
229	800FM: Illum PBs/Mush, Non-Illum Mush
22F	140MG: MCP J Frame
22H	SMC-3, Enclosed
230	800C: Pendant Station Products
231	800F: Miscellaneous
232	800FM: Illuminated Selector Switches
235	800G: Push Buttons, Zone1/2/Div 2
23F	140MG: MCP K Frame
23H	SMC-FLEX, Enclosed
243	Spare Parts - NEMA Products
246	193-K: Bimetal Overload
248	193-T: Bimetal Overload
249	193: Bimetal Overload, Accessories
24H	SMC-50: Enclosed
24J	Configurable Safety Relays
250	141A: Bus Bar
254	100/104-C: Contactors, 30-37A, AC
255	100/104-C: Contactors, 43A, AC

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
256	100/104-C: Contactors, 60-85A
258	100-C/700-CF: Aux Contacts
259	100-L: Lighting Contactors
25G	Flex 5000 I/O
25J	840E & 839E Level & Flow
260	100/104/M/K: AC Mini Contactors
26E	PF520 Series External EMC Filter
26F	MPCB 140G H Frame
26G	Flex 5000 XT I/O
26J	MCCB - 140UT-D
274	Timer Accessories
275	194C/E/L: Accessories
276	194C/L: Switches and Handles
277	194R: Switches, Enclosed
278	194R: UL Disc. Switches
27E	PF520 Series Optional Communication Card
27F	MPCB 140G J Frame
27G	Starting Torque Controller: Bulletin 154
27H	Hazardous Location Devices & Metal Horns
280	198: Enclosures & Accessories
283	140U/M: External Accessories
28E	PF520 Series Options & Accessories
28H	700-K: Mini Control Relays
298	190/191: Eco 2C Starters
299	109/105/etc: Miscellaneous Starters
29H	140MG: MCP 125 & 225A
300	103S/107S/103T/107T: Std Starters, 2C/3C
301	140M/MT/ME Accessories
307	140M-D: Motor Protectors
30G	189/1492-SPM: Circ. Prot. Accessories
30H	140MG: MCP 800 & 1200A
31H	188: MCB & Accessories
330	NEMA Push Buttons, 800T Type 4/13
331	NEMA Push Buttons, 800H Type 4/4X/13
33A	Micro 400 Light Curtain
33H	IEC Contactors, Coils & Contact Kits
347	XL Standard Power Supply
348	XLE/XLD Essential Power Supply
349	XLP Compact Power Supply
34H	100/104/100S-E: Contactors, 860-2650 A
350	XLS Performance Power Supply
351	P Series UPS, Double Conversion On-line
352	S Series UPS, Basic DIN Rail
353	U Series UPS, Feature DIN Rail
354	Uninterruptible Power Sup, Accessories
41E	1608S: I-Sense

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
41F	Stratix 5400 & 5410 & Stratix 5800 Expansion Module
42F	PF527: 1 Phase, 115V, 230V
42J	Stratix 5800 Managed Switch
44B	42CB, 42CD, 42CM, 42CF, 42CS Sensors
45B	43G and 43P Fiber Optic Cables
46H	700-H: Plug-in Timing Relays
48H	IEC Enclosed Starters & Accs.
49H	1492-J: Screw Terminal Blocks
50H	Miniature Photoelectrics
51H	42CRC, 42QA, Ser 9000/10000, 45LMS, Kits
52H	873: Ultrasonic Sensors
53H	440L: Guardshield Light Curtains
548	1408/1420/1426: Power Monitors
54H	445L: Guardshield Light Curtains
55H	450L: Guardshield Light Curtains
55J	Interface Modules, Wiring Systems
56F	30-100 AMP Universal Disconnect Switch
56J	1492-J/L/P: Terminal Block Accessories
570	Condition Monitors
571	Data Collectors
577	NCPU Sensors
579	Accelerometers & Accessories
57H	442G: Multifunctional Access Box
57J	SMC Spare Parts & Accessories
580	Other Accessories
58J	SMC-3, Open, 1-85A
59E	Power Monitor Accessories
59G	600 AMP Universal Disconnect Switch
59H	802: Limit Switches
59J	141C: Crossboard Bus Bar
609	801, 802T: Limit Switches & Levers
60F	836P and 837T Pressure and Temperature
60H	844/845: Encoders
60J	PF523: 1 Phase Frame A & B
613	842: Encoders
615	845 Accessories
616	45MLD, 45PVA, 45AST: Fork & Label Sensor
617	Miniature, Bkgrnd Suppress, DIN Mount FO
619	General Purpose Proximity Sensor
61J	PF523: 3 Phase Frame A & B
620	871Ti/871TM: Specialty Prox Sensors
621	872C: World Prox Sensors
622	Ser 9000, RightSight, Cylindrical Sensor
623	Series 4000, 5000, 6000 and 7000 Sensors
625	MultiSight, Laser and Ultrasonic Sensors
62J	PF523: 3 Phase Frame C & D

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
631	440T: Trapped Key Interlocks
635	440A: Safety Accessories
636	440K: Key Interlocks
637	440E: E-Stop & Cable Pull Switches
638	440G: Guardlocking Interlocks
639	440H: Hinge Interlocks
640	440N: Non-Contact Switch (FerroGuard)
641	440N: Non-Contact Switch (SensaGuard)
642	440P: Position Limit Switches
644	440R: MSR Single Function Safety Relays
645	879/888/889/898: Std Connection Systems
646	871A: Terminal Chambers
648	1585: E-Net Rnd Media
65H	1485: DeviceNet Media
65J	PF525: 1 Phase Frame A & B
66E	EtherNet/IP Encoders
66H	Motor Protectors - 140MT-C
66J	PF525: 3 Phase Frame A & B
67H	Motor Protectors -140MT-D
67J	PF525: 3 Phase Frame C & D
68G	100/104-E: Contactors, 9-16A
68H	PF755T FRAME 5
69G	100/104-E: Contactors, 26-38A
69H	PF755T FRAME 6
69J	PF527: 3 Phase Frame A & B
70A	Electronic Circuit Protection
70H	PF755T FRAME 7
70J	PF527: 3 Phase Frame C & D
71A	Stratix 5200 & Stratix 5700
71H	PF755T FRAME 8-10
72H	PF755T FRAME 11-15
74F	Load Break Switches, Enclosed
75F	Pump Panels, SMC
77A	109/105 Compact Class Non-Combination Starters
77J	Pck DRV: PF 755/755TS (> frame 8)
78A	103C/107C Compact Class Combination Starters
78H	Stratix 4300
791	440R: Specialty Safety Relays
798	100/104-C: Contactors, 23A, AC
79F	XLB Basic Power Supply
79G	PowerFlex 755TS FR1-3
800	140M-C: Motor Protectors
801	140M-F: Motor Protectors
80G	PowerFlex 755TS FR4-6
81F	100/104/100S-E: Contactors, 116-146 A
81G	PowerFlex 755TS FR7

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
820	800FP: Incandescent Models/Selector Jog
821	800F: LED Modules/Replacement Bulbs
822	800FP: Legnd Frame/Plate, Rplmt Lens/Key
823	800FP: POTS/III-Mushr/Contact Blocks
824	800FP: Illum PBs/Mush, Non-Illum Mush
825	800FP: Key SS/Non-III Mult/PBs/Reset
826	800FP: Non-III SS/Pilot Lights/Rods
827	800FP: Illum Selector Sw/E-Stop Legends
828	800F: Accessories
829	800F: Key SS/Non-III Mult/PBs/Reset/Togl
82F	100/104/100S-E: Contactors, 190-205 A
830	800FM: Non-III Selctr Swtch/Pilot Lights
834	140F: Fuse Holders
837	100/104-C: Contactors, 23A, DC
839	100/104-C: Contactors, 30-37A, DC
83F	100/104/100S-E: Contactors, 265-370 A
83G	Motor Protectors -140MP-A
840	100/104-C: Contactors, 43A, DC
841	105/170 Wiring Kits
842	194R: Accessories
843	194E: Switches and Handles
845	140M: Compact Bus Bar
847	Spare Parts - IC
84F	100/104/100S-E: Contactors, 400-460 A
852	100/104-C: Contactors, 60-85A, DC
856	54RF, 55RF, 56RF: RFID Products
85F	100/104/100S-E: Contactors, 580-750, 1260 A
85G	Motor Protectors - 140MP Accessories
85H	PF755TM Non-Regen Supply Frame 8-9
86G	100/104-E: Contactors, 40-96A
86H	Armor knx
87A	PF753: 0.75 kW -7.5 kW, 400V, Frame 1
88A	PF753: 1 HP -10 HP, 480V, Frame 1
88F	IEC Contactors, Accessories > 100 A
88G	100-E/700-EF: Accessories
88H	190/191/140MT Enclosed Starters
88J	MagneMotion
89A	PF755: 0.75 kW -7.5 KW, 400V, Frame 1
89H	190/191 Open Starters
909	IP66 On-Machine Power Supply
90A	PF755: 1 HP -10 HP, 480V, Frame 1
90G	700-EF&700S-EF Industrial Control Relays
914	4983: Surge Protective Devices
915	4983: Filters
919	100/104-C/R: Contactors, 16A, AC
91J	MagneMotion cable

ROKLIVE Q2 EXTRA 15% PROMOTION

PGC	PGC Name
920	100/104-C/R: Contactors, 9A, AC
921	100-K/M, 700-K/M: Accessories
922	100/104/M/K: DC Mini Contactors
932	700-CF/R: Control Relays AC
933	700-CF/R: Control Relays DC
934	194R: IEC Disc. Switches
941	100/104-C/R: Contactors, 12A, AC
942	100/104-C/R: Contactors, 9A, DC
943	100/104-C/R: Contactors, 16A, DC
944	100/104-C/R: Contactors, 12A, DC
945	194R: Handles
95G	Armor knx cable
963	Modified Industrial Control Products
96H	ArmorBlock 5000 I/O
994	Sensing Light Arrays