

Specifications LC-075-XXX



Performance Parameters	Symbol	Units	LC-075-100			LC-075-200			LC-075-300			LC-075-400			LC-075-600			LC-075-800																						
			NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC																				
Cooling Method			NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC																				
Continuous Force ¹	F _{cTmax}	N (lbf)	193 (43)	241 (54)	289 (65)	385 (87)	481 (108)	578 (130)	578 (130)	722 (162)	867 (195)	770 (173)	963 (216)	1155 (260)	1155 (260)	1444 (325)	1733 (390)	1541 (346)	1926 (433)	2311 (519)																				
Peak Force ²	F _p	N (lbf)	441 (99)	441 (99)	441 (99)	882 (198)	882 (198)	882 (198)	1368 (308)	1368 (308)	1368 (308)	1824 (410)	1824 (410)	1824 (410)	2736 (615)	2736 (615)	2736 (615)	3649 (820)	3649 (820)	3649 (820)																				
Motor Constant ¹	K _M	N/√-W (lbf/√-W)	19.8 (4.4)	19.8 (4.4)	19.8 (4.4)	27.9 (6.3)	27.9 (6.3)	27.9 (6.3)	34.2 (7.7)	34.2 (7.7)	34.2 (7.7)	39.5 (8.9)	39.5 (8.9)	39.5 (8.9)	48.4 (10.9)	48.4 (10.9)	48.4 (10.9)	55.9 (12.6)	55.9 (12.6)	55.9 (12.6)																				
Thermal Resistance	R _{th}	°C/W	1.16	0.74	0.51	0.58	0.37	0.26	0.39	0.25	0.17	0.29	0.19	0.13	0.19	0.12	0.09	0.14	0.09	0.06																				
Max Power Dissipation	P _{cTmax}	W	95	148	214	190	297	428	285	445	641	380	594	855	570	891	1283	760	1188	1711																				
Maximum Applied Bus Voltage ⁷	V _{DC}	Volts	650			650			650			650			650			650																						
Electrical Cycle Length	E _c	mm	50			50			50			50			50			50																						
Electrical Time Constant	τ _e	msec	10			10			10			10			10			10																						
Maximum Coil Temperature	T _{max}	°C	130			130			130			130			130			130																						
Winding Type			D		E		D		E		D		E		D		E		D		E																			
Force Constant ^{1,6}	K _F	N/A _{pk} (lbf/A _{pk})	45.5 (10.2)		N/A		45.5 (10.2)		91.0 (20.5)		45.5 (10.2)		136.5 (30.7)		45.5 (10.2)		91.0 (20.5)		45.5 (10.2)		91.0 (20.5)																			
Back EMF Constant p-p ^{3,4,6}	K _e	V _p /m/s (V _p /in/s)	53.7 (1.37)		N/A		53.7 (1.37)		107.5 (2.73)		53.7 (1.37)		161.2 (4.10)		53.7 (1.37)		107.5 (2.73)		53.7 (1.37)		107.5 (2.73)																			
Peak Current ⁴	I _p	A _{pk} (A _{rms})	11.5 (8.1)		N/A		22.9 (16.2)		11.5 (8.1)		35.6 (25.1)		11.9 (8.4)		47.4 (33.5)		23.7 (16.8)		71.1 (50.3)		35.6 (25.1)		94.8 (67.0)		47.4 (33.5)															
Cooling Type			NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC	NC	AC	WC					
Continuous Current ^{1,4}	I _{cTmax}	A _{pk} (A _{rms})	4.2 (3.0)	5.3 (3.7)	6.3 (4.5)	N/A	N/A	N/A	8.5 (6.0)	10.6 (7.5)	12.7 (9.0)	4.2 (3.0)	5.3 (3.7)	6.3 (4.5)	12.7 (9.0)	15.9 (11.2)	19.0 (13.5)	4.2 (3.0)	5.3 (3.7)	6.3 (4.5)	16.9 (12.0)	21.2 (15.0)	25.4 (18.0)	8.5 (6.0)	10.6 (7.5)	12.7 (9.0)	15.9 (11.2)	19.0 (13.5)	25.4 (18.0)	31.7 (22.4)	38.1 (26.9)	12.7 (9.0)	15.9 (11.2)	19.0 (13.5)	33.9 (23.9)	42.3 (29.9)	50.8 (35.9)	16.9 (12.0)	21.2 (15.0)	25.4 (18.0)
Resistance p-p ^{3,6} @20°C	R ₂₀	ohm	4.94		N/A		2.47		9.88		1.65		14.82		1.24		4.94		0.82		3.29		0.62		2.47															
Inductance p-p ³	L	mH	47		N/A		24		95		16		142		12		47		8		32		6		24															
Mechanical Parameters																																								
Magnetic Attraction ⁸	F _a	N (lbf)	1000 (225)			2000 (450)			2999 (674)			3999 (899)			5999 (1349)			7998 (1798)																						
Coil Mass ⁵	M _c	kg (lb _m)	2.4 (5.2)	2.6 (5.8)	2.6 (5.8)	4.2 (9.2)	4.6 (10.3)	4.6 (10.3)	6.0 (13.2)	6.7 (14.7)	6.7 (14.7)	7.8 (17.1)	8.7 (19.1)	8.7 (19.1)	11.3 (24.9)	12.5 (27.7)	12.5 (27.7)	14.9 (32.8)	16.5 (36.4)	16.5 (36.4)																				
Magnetic Track Mass	M _n	kg/m (lb/in)	9.0 (0.5)			9.0 (0.5)			9.0 (0.5)			9.0 (0.5)			9.0 (0.5)			9.0 (0.5)																						

Notes: NC= No Cooling, AC= Air Cooling, WC = Water Cooling

Motor performance specifications are with sinusoidal commutation.

¹ Continuous forces, motor constant and current listed are with coils at maximum temperature 130°C, mounted to a 1" aluminum heat sink whose area is noted in the table, and at 20°C ambient.

² Max on time 1 sec. In certain applications, the motor may produce significantly higher peak forces. Please contact Anorad Applications Engineering for details.

³ All winding parameters listed are measured line-to-line (phase-to-phase).

⁴ All currents and voltages listed are measured 0-peak of the sine wave unless noted rms.


⁵ AC and WC include mass of cooling plate. Consult Anorad for Flow and Pressure for air cooled and water cooled version.

⁶ All specifications are ±10%. Phase-to-phase inductance is ±30%.

⁷ Maximum cable length 10 meters. Please consult factory concerning applications requiring longer cables.

⁸ All specifications are at the standard referenced air gap.

Motor Phasing Diagram



Note: Phasing direction is coil moving towards motor power cable.