

Australian Declaration of Conformity

The undersigned, representing the following
Manufacturer

and the RA Authorised Supplier within Australia

Rockwell Automation, Inc.
6400 West Enterprise Drive
Mequon, WI 53092
USA

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic. 3130
Australia

Supplier Code Number (SCN): N223

Australian Company Number (ACN): 005 549 477

herewith declare that the Products
Product identification (brand and
catalogue number/part number):

Configured Drive Package (Adjustable Frequency Drives)
Allen-Bradley PowerFlex 40 Standard Packaged Drive
Program
(reference the attached list of catalogue numbers)

are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation.

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

EN 61800-3: 1996 with A11: 2000

Adjustable Speed Electrical Power Drive Systems – Part 3: EMC Product
Standard Including Specific Test Methods

Detailed Technical Information is maintained at:

Rockwell Automation, Inc
6400 West Enterprise Drive
Mequon, WI 53092
USA

Compliance Folder is maintained at:



Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic 3130
Australia

Document No.: AU-DST-0074-A-EN

Document No.: AUS-0128-A

Manufacturer:

Authorised Person within Australia:



Signature

Signature

Name: Daniel Stewart
Position: Manager, Product Certification
Engineering
Date: 29-Mar-2005

Name: William Grant Roberts
Position: Managing Director
Date: 05-APR-2005

<i>Catalogue Number¹</i>	<i>Series²</i>	<i>Description</i>
23B-D1P4C10*		AC Drive, 0.5 Hp, 480V, 3 Phase, , Type 4X (IP66)
23B-D2P3C10*		AC Drive, 1 Hp, 480V, 3 Phase, , Type 4X (IP66)
23B-D4P0C10*		AC Drive, 2 Hp, 480V, 3 Phase, , Type 4X (IP66)
23B-D6P0C10*		AC Drive, 3 Hp, 480V, 3 Phase, , Type 4X (IP66)
23B-D010C10*		AC Drive, 5 Hp, 480V, 3 Phase, , Type 4X (IP66)
23B-D012C10*		AC Drive, 7.5 Hp, 480V, 3 Phase, , Type 4X (IP66))
23B-D017C10*		AC Drive, 10 Hp, 480V, 3 Phase, , Type 4X (IP66)
23B-D024C10*		AC Drive, 15 Hp, 480V, 3 Phase, Type 4X (IP66)
23B-D1P4D10*		AC Drive, 0.5 Hp, 480V, 3 Phase, Type 4/12 (IP66)
23B-D2P3D10*		AC Drive, 1 Hp, 480V, 3 Phase, Type 4/12 (IP66)
23B-D4P0D10*		AC Drive, 2 Hp, 480V, 3 Phase, Type 4/12 (IP66)
23B-D6P0D10*		AC Drive, 3 Hp, 480V, 3 Phase, Type 4/12 (IP66)
23B-D010D10*		AC Drive, 5 Hp, 480V, 3 Phase, Type 4/12 (IP66)
23B-D012D10*		AC Drive, 7.5 Hp, 480V, 3 Phase Type 4/12 (IP66)
23B-D017D10*		AC Drive, 10 Hp, 480V, 3 Phase, Type 4/12 (IP66)
23B-D024D10*		AC Drive, 15 Hp, 480V, 3 Phase, Type 4/12 (IP66)

Published Product Options

- E22 DeviceNet Quick Disconnect (Bottom)
- E23 DeviceNet Quick Disconnect (Left Side)
- J10 ZAC Master (Left to Right)
- J11 ZAC Master (Right to Left)
- J12 ZAC Infeed (Left to Right)
- J13 ZAC Infeed (Right to Left)
- J14 Intermediate (Left to Right)
- J15 Intermediate (Right to Left)
- P3 Motor Circuit Protector
- P6 Drive Disconnect Switch – Fused
- R3 DeviceNet I/O 4 In/2 Out with Hand/Off/Auto Selector Switch
- R4 DeviceNet Point I/O wIB4
- R5 -R3 plus 4 I/O Quick Disconnect
- S1 Hand/Off/Auto S.S. (Start/Stop/Speed Ref.)
- S4 Auto/Manual S.S. (Speed Ref.)
- S7 Start and Stop P.B.
- S8 Forward/Reverse S.S.
- S20 Local Control with Off/Run FWD and a Local/Remote S.S.
- S21 Local/Off/Remote with 1 N.O. Interposing Relay

¹ * may be **4, D, E, or P** indicating drive enclosure options.

² Products of the series level shown or higher are certified. If no series number is given, then all series are covered.