

Australian Declaration of Conformity

The undersigned, representing the following
Manufacturers

Rockwell Automation, Inc.
6400 W. Enterprise Drive
Mequon, Wisconsin 53092
USA

Rockwell Automation Korea Ltd.
447-6 Gongsi-ri
Giheung-eup
Yongin-city, Kyonggi-do 449-902
Republic of Korea

Supplier Code Number (SCN): N223

and the RA Authorised Supplier within Australia

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic. 3130
Australia

Australian Company Number (ACN): 005 549 477

herewith declare that the Products
Product identification (brand and
catalogue number/part number):

Digital Servo Drives and Accessories Kinetix 2000/CSDM
Allen-Bradley Bulletin 2093
OEMax CSDM
(reference the attached list of catalogue numbers)

are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation:

Radiocommunications Act: 1992

Radiocommunications (Electromagnetic Compatibility) Standard: 1998

Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998

and that the standards and/or technical specifications referenced below have been applied:

AS/NZS CISPR 11: 2002
(Group 2, Class A)

Limits and Methods of Measurement of electronic disturbance characteristic
of industrial, scientific, and medical (ISM) radio frequency equipment

Detailed Technical Information is maintained at:

Rockwell Automation, Inc.
6400 W. Enterprise Drive
Mequon, Wisconsin 53092
USA

Compliance Folder is maintained at:

Rockwell Automation Australia Ltd.
37 Chapman Street (PO Box 190)
Blackburn, Vic 3130
Australia

Document No.: AU-IMC-0023-A-EN

Document No.: AUS-0151-A

Manufacturer:

Authorised Person within Australia:

Signature



Signature



Name: Tom Van Groll
Position: Manager Engineering
Date: 28-June-2007

Name: Donald Timothy Werner
Position: Managing Director
Date: 28-July-2007

¹ Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

² Total output cable length, power or feedback attached to the drive must not exceed 160 meters. Any one cable may not exceed 30 meters.

<i>Catalogue Number</i>	<i>Series ¹</i>	<i>Description</i>
Bulletin 2093 Servo Drives ²		
2093-AC05-MP1		<i>Bulletin 2093 3kW/1A Integrated Axis Module</i>
2093-AC05-MP2		<i>Bulletin 2093 3kW/2A Integrated Axis Module</i>
2093-AC05-MP5		<i>Bulletin 2093 3kW/3A Integrated Axis Module</i>
2093-AMP1		<i>Bulletin 2093 1A Axis Module</i>
2093-AMP2		<i>Bulletin 2093 2A Axis Module</i>
2093-AMP5		<i>Bulletin 2093 3A Axis Module</i>
2093-AM01		<i>Bulletin 2093 6A Axis Module</i>
2093-AM02		<i>Bulletin 2093 9.5A Axis Module</i>
2093-ASPO6		<i>Bulletin 2093 Shunt Module</i>
2093-PRS1		<i>Bulletin 2093 1Axis Power Rail</i>
2093-PRS2		<i>Bulletin 2093 2Axis Power Rail</i>
2093-PRS3		<i>Bulletin 2093 3Axis Power Rail</i>
2093-PRS4		<i>Bulletin 2093 4Axis Power Rail</i>
2093-PRS5		<i>Bulletin 2093 5Axis Power Rail</i>
2093-PRS7		<i>Bulletin 2093 7Axis Power Rail</i>
2093-PRS8S		<i>Bulletin 2093 8Axis Power Rail</i>
2093-PRF		<i>Bulletin 2093 Slot Filler</i>
OEMax CSDM Servo Drives ²		
CSDM-IAM-01BX1		<i>CSDM 3kW/1A Integrated Axis Module</i>
CSDM-IAM-02BX1		<i>CSDM 3kW/2A Integrated Axis Module</i>
CSDM-IAM-04BX1		<i>CSDM 3kW/3A Integrated Axis Module</i>
CSDM-AM-01BX1		<i>CSDM 1A Axis Module</i>
CSDM-AM-02BX1		<i>CSDM 2A Axis Module</i>
CSDM-AM-04BX1		<i>CSDM 3A Axis Module</i>
CSDM-AM-08BX1		<i>CSDM 6A Axis Module</i>
CSDM-AM-15BX1		<i>CSDM 9.5A Axis Module</i>
CSDM-SMA		<i>CSDM Shunt Module</i>
CSDM-PRA1		<i>CSDM 1Axis Power Rail</i>
CSDM-PRA2		<i>CSDM 2Axis Power Rail</i>
CSDM-PRA3		<i>CSDM 3Axis Power Rail</i>
CSDM-PRA4		<i>CSDM 4Axis Power Rail</i>
CSDM-PRA5		<i>CSDM 5Axis Power Rail</i>
CSDM-PRA7		<i>CSDM 7Axis Power Rail</i>
CSDM-PRA8		<i>CSDM 8Axis Power Rail</i>
CSDM-SFA		<i>CSDM Slot Filler</i>

¹ Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

² Total output cable length, power or feedback attached to the drive must not exceed 160 meters. Any one cable may not exceed 30 meters.