

EC Declaration of Conformity

The undersigned, representing the manufacturer

Rockwell Automation, Inc.
1201 South Second Street
Milwaukee, Wisconsin 53204
USA

*and the authorised representative established within the
Community*

Rockwell Automation BV
Rivium 1e Straat, 23
2209 LE Capelle aan den IJssel
Netherlands

herewith declare that the Products

IEC Miniature Circuit Breakers, 0.5 – 40 A

*Product identification (brand and
catalogue number/part number):*

Allen-Bradley 1492-SP Series
(reference the attached catalogue nomenclature)

*are in conformity with the essential requirements of the following EC Directive(s) when installed in accordance with
the installation instructions contained in the product documentation:*

2006/95/EC

Low Voltage Directive

and that the standards and/or technical specifications referenced below have been applied:

EN 60898-1:2003 + A1:2004


*Electrical accessories – Circuit-breakers for overcurrent protection for
household and similar installations – Part 1: Circuit-breakers for a.c.
operation*

Year of CE Marking (Low Voltage Directive):

2001


Manufacturer:

Authorised Representative in the Community:



Signature

Name: Daniel L. Nachtigall
Position: Supv – Product Certification Engineering
Date: 04-Nov-2009



Signature

Name: Viktor Schiffer
Position: Engineering Manager
Date: 03-Dec-2009

<i>Catalogue number</i>	<i>Series ¹</i>	<i>Description</i>
1492-SPxxxx	C	IEC miniature circuit breakers per Nomenclature

1) If no series number is given, then all series are covered.

NOMENCLATURE:

1492-SP	-	3	C	150	N
1		2	3	4	5

1	Product Line 1492-SP – Miniature circuit breaker
2	Number of Poles 1 – 1 pole 2 – 2 pole 3 – 3 pole 4 – 4 pole
3	Trip Curve B – Resistive or slightly inductive C – Inductive D – Highly inductive
4	Current Rating 005 – 0.5 A 050 – 5.0 A 160 – 16.0 A 010 – 1.0 A 060 – 6.0 A 200 – 20.0 A 015 – 1.5 A 070 – 7.0 A 250 – 25.0 A 020 – 2.0 A 080 – 8.0 A 300 – 30.0 A 025 – 2.5 A 100 – 10.0 A 320 – 32.0 A 030 – 3.0 A 120 – 12.0 A 400 – 40.0 A 035 – 3.5 A 130 – 13.0 A 040 – 4.0 A 150 – 15.0 A
5	Options N – Switched neutral