

***Australian Declaration of Conformity***

*The undersigned, representing the following  
Manufacturer*

*and the RA Authorised Supplier within Australia*

**Rockwell Automation, Inc.  
6400 W. Enterprise Drive  
Mequon, WI 53092  
USA**

**Rockwell Automation Australia Ltd.  
37 Chapman Street (PO Box 190)  
Blackburn, Vic. 3130  
Australia**

**Supplier Code Number (SCN): N223**

**Australian Company Number (ACN): 005 549 477**

*herewith declare that the Products  
Product identification (brand and  
catalogue number/part number):*

**Adjustable Frequency AC Drives  
Allen-Bradley PowerFlex 70**  
*(reference the attached list of catalogue numbers)*

*are in conformity with the following when installed in accordance with the installation instructions contained in the product documentation:*

*Radiocommunications Act: 1992*

*Radiocommunications (Electromagnetic Compatibility) Standard: 1998*

*Radiocommunications (Compliance Labelling - Incidental Emissions) Notice: 1998*

*and that the standards and/or technical specifications referenced below have been applied:*

*EN 61800-3:2004*

*Adjustable Speed Electrical Power Drive Systems – Part 3: EMC Product  
Standard Including Specific Test Methods*

*Detailed Technical Information is maintained at:*

Rockwell Automation, Inc.  
6400 W. Enterprise Drive  
Mequon, WI 53092  
USA

*Compliance Folder is maintained at:*

Rockwell Automation Australia Ltd.  
37 Chapman Street (PO Box 190)  
Blackburn, Vic 3130  
Australia


*Document No.: AU-DST-0025-E-EN*

*Document No.: AUS-0045-E*

*Manufacturer:*

*Authorised Person within Australia:*

*Signature*



*Name:* Daniel Stewart  
*Position:* Manager, Product Certification  
Engineering  
*Date:* 26-Feb-2007

*Signature*



*Name:* Donald Timothy Werner  
*Position:* Managing Director  
*Date:* 2-Mar-2007

<i>Catalogue number<sup>1</sup></i>	<i>Series<sup>2</sup></i>	<i>Description</i>
<b>Adjustable Frequency AC Drives</b>		
20AB2P2x*****		AC Drive, 0.5 Hp, 240V, 3 Phase
20AB4P2x*****		AC Drive, 1 Hp, 240V, 3 Phase
20AB6P8x*****		AC Drive, 2 Hp, 240V, 3 Phase
20AB9P6x*****		AC Drive, 3 Hp, 240V, 3 Phase
20AB015x*****		AC Drive, 5 Hp, 240V, 3 Phase
20AB022x*****		AC Drive, 7.5 Hp, 240V, 3 Phase
20AB028x*****		AC Drive, 10 Hp, 240V, 3 Phase
20AB042x*****		AC Drive, 15 Hp, 240V, 3 Phase
20AB054x*****		AC Drive, 20 Hp, 240V, 3 Phase
20AB070x*****		AC Drive, 25 Hp, 240V, 3 Phase
20AC1P3x*****		AC Drive, 0.5 Hp, 400V, 3 Phase
20AC2P1x*****		AC Drive, 1 Hp, 400V, 3 Phase
20AC3P5x*****		AC Drive, 2 Hp, 400V, 3 Phase
20AC5P0x*****		AC Drive, 3 Hp, 400V, 3 Phase
20AC8P7x*****		AC Drive, 5 Hp, 400V, 3 Phase
20AC011x*****		AC Drive, 7.5 Hp, 400V, 3 Phase
20AC015x*****		AC Drive, 10 Hp, 400V, 3 Phase
20AC022x*****		AC Drive, 15 Hp, 400V, 3 Phase
20AC030x*****		AC Drive, 20 Hp, 400V, 3 Phase
20AC037x*****		AC Drive, 25 Hp, 400V, 3 Phase
20AC043x*****		AC Drive, 30 Hp, 400V, 3 Phase
20AC060x*****		AC Drive, 40 Hp, 400V, 3 Phase
20AC072x*****		AC Drive, 50 Hp, 400V, 3 Phase
20AD1P1x*****		AC Drive, 0.5 Hp, 480V, 3 Phase
20AD2P1x*****		AC Drive, 1 Hp, 480V, 3 Phase
20AD3P4x*****		AC Drive, 2 Hp, 480V, 3 Phase
20AD5P0x*****		AC Drive, 3 Hp, 480V, 3 Phase
20AD8P0x*****		AC Drive, 5 Hp, 480V, 3 Phase
20AD011x*****		AC Drive, 7.5 Hp, 480V, 3 Phase
20AD014x*****		AC Drive, 10 Hp, 480V, 3 Phase
20AD017x*****		AC Drive, 10 Hp, 480V, 3 Phase
20AD022x*****		AC Drive, 15 Hp, 480V, 3 Phase
20AD027x*****		AC Drive, 20 Hp, 480V, 3 Phase
20AD034x*****		AC Drive, 25 Hp, 480V, 3 Phase
20AD040x*****		AC Drive, 30 Hp, 480V, 3 Phase
20AD052x*****		AC Drive, 40 Hp, 480V, 3 Phase
20AD065x*****		AC Drive, 50 Hp, 480V, 3 Phase
<b>Drive Interface Modules</b>		
20-HIM-A1		Digital LED Drive Interface Module
20-HIM-A2		Digital LCD Drive Interface Module
20-HIM-A3		Full Numeric LCD Drive Interface Module
20-HIM-A4		Analog LCD Drive Interface Module
20-HIM-A5		Programmer Only LCD Drive Interface Module
20-HIM-C3		Panel Mount Full Numeric LCD Drive Module (IP66)
20-HIM-C5		Panel Mount Programmer Only LCD Drive Module (IP66)
20-HIM-C3S		Panel Mount Full Numeric LCD Drive Module (IP66)
20-HIM-C5S		Panel Mount Programmer Only LCD Drive Module (IP66)

<sup>1</sup> x may be **A**, **C** or **F** indicating drive enclosure options, \* may be **any number or letter** indicating drive options which do not impact this DoC

<sup>2</sup> Products of the series level shown or higher are certified. If no series number is given, then all series are covered.

<i>Catalogue number<sup>1</sup></i>	<i>Series<sup>2</sup></i>	<i>Description</i>
Communication Modules		
20-COMM-D		<i>DeviceNet Comm Module</i>
20-COMM-R		<i>Remote I/O Comm Module</i>
20-COMM-S		<i>RS-485 Serial Comm Module</i>
20-COMM-H		<i>RS-485 Serial Comm Module (HVAC)</i>
20-COMM-C		<i>ControlNet Comm Module</i>
20-COMM-E		<i>Ethernet Comm Module</i>
20-COMM-M		<i>Modbus / TCP Comm Module</i>
20-COMM-Q		<i>Fiber Optic Comm Module</i>
20-XCOMM-IO-OPT1		<i>Digital I/O</i>
1203-SSS		<i>Serial to Scanport Converter</i>
RFI Filters		
20A-RF-08-A1		<i>Line Filter, 0.5-1 Hp, 200-240V, 1 Phase</i>
20A-RF-05-A3		<i>Line Filter, 0.5-2 Hp, 230-460V, 3 Phase</i>

<sup>1</sup> **x** may be **A**, **C** or **F** indicating drive enclosure options, \* may be **any number or letter** indicating drive options which do not impact this DoC

<sup>2</sup> Products of the series level shown or higher are certified. If no series number is given, then all series are covered.