

EC Declaration of Conformity

The undersigned, representing the manufacturer

Rockwell Automation, Inc.
1201 South 2nd Street
Milwaukee, Wisconsin 53204
USA

*and the authorised representative established within the
Community*

Rockwell Automation BV
Rivium 1e Straat, 23
2209 LE Capelle aan den IJssel
Netherlands

herewith declare that the Products: **IEC Miniature Circuit Breakers, 50 – 63 A**

*Product identification (brand and
catalogue number/part number):*

Allen-Bradley 1492-SP Series
(reference the attached catalogue nomenclature)

*are in conformity with the essential requirements of the following EC Directive(s) when installed in accordance with
the installation instructions contained in the product documentation:*

2006/95/EC *Low Voltage Directive*

and that the standards and/or technical specifications referenced below have been applied:


EN 60947-1:2007 *Low-voltage switchgear and controlgear – Part 1: General rules*

EN 60947-2:2006 *Low-voltage switchgear and controlgear – Part 2: Circuit-breakers*

Year of CE Marking (Low Voltage Directive): 2001


Manufacturer:

Authorised Representative in the Community:



Signature

Name: Daniel L. Nachtigall
Position: Supv – Product Certification Engineering
Date: 04-Nov-2009



Signature

Name: Viktor Schiffer
Position: Engineering Manager
Date: 30-Nov-2009

| <i>Catalogue number</i> | <i>Series ¹</i> | <i>Description</i> |
|-------------------------|----------------------------|-------------------------------------------------|
| 1492-SPxxxx | | IEC miniature circuit breakers per Nomenclature |

1) If no series number is given, then all series are covered.

NOMENCLATURE:

| | | | | | |
|---------|---|---|---|-----|---|
| 1492-SP | - | 3 | C | 150 | N |
| 1 | | 2 | 3 | 4 | 5 |

| | |
|---|-------------------------------------------------------------------------|
| 1 | Product Line 1492-SP – Miniature circuit breaker |
| 2 | Number of Poles 1 – 1 pole 2 – 2 pole 3 – 3 pole 4 – 4 pole |
| 3 | Trip Curve D – Highly inductive |
| 4 | Current Rating 500 – 50.0 A 630 – 63.0 A |
| 5 | Options N – Switched neutral |