

EC Declaration of Conformity

The undersigned, representing the manufacturer

Rockwell Automation, Inc.
1201 South 2nd Street
Milwaukee, WI 53204
USA

*and the authorised representative established within the
Community*

Rockwell Automation European Headquarters SA/NV
Vorstlaan/Boulevard du Souverain 36 - BP 3A/B
B-1170 Brussels
Belgium

herewith declare that the Products **Armor Point I/O Product Family**

*Product identification (brand and
catalogue number/part number):* **Allen-Bradley 1738 Series**
(reference the attached list of catalogue numbers)

*are in conformity with the provisions of the following EC Directive(s) when installed in accordance with the
installation instructions contained in the product documentation:*

2006/95/EC *Low Voltage Directive (LVD)*
2004/108/EC *Electromagnetic Compatibility Directive (EMCD)*

and that the standards and/or technical specifications referenced below have been applied (as indicated):

EN 61131-2:2003 *Programmable Controllers - Part 2: Equipment Requirements and Tests
(Clause 8 [Zone A & B, EMCD] and Clause 11 [LVD])*

EN 61326-1:2006 *Electrical Equipment For Measurement, Control, and Laboratory Use -
Industrial EMC Requirements*

EN 61000-6-2:2005 *Electromagnetic Compatibility (EMC) - Part 6-2: Generic Standards -
Immunity for Industrial Environments*


EN 61000-6-4:2001 *Electromagnetic Compatibility (EMC) - Part 6-4: Generic Standards -
Emission Standard for Industrial Environments (Class A)*

Year of CE Marking (Low Voltage Directive): 2004

Manufacturer: *Authorised Representative in the Community:*


Signature

Name: John R. Mowry
Position: Compliance Engineer
Date: 06-Jul-2008


Signature

Name: Viktor Schiffer
Position: Engineering Manager
Date: 14-Aug-2008

Catalogue number	Series ¹	Description	Directive ²	
			EMC	LVD
1738-232ASCM12		M12-style, RS232 ASCII Interface Module	YES	N/R
1738-485ASCM12		M12-style, RS485/422 ASCII Interface Module	YES	N/R
1738-8CFGDLXM12		M12-style, 8 Channel, 24Vdc Configurable I/O Module w/DeviceLogix	YES	N/R
1738-8CFGDLXM23		M23-style, 8 Channel, 24Vdc Configurable I/O Module w/DeviceLogix	YES	N/R
1738-8CFGDLXM8		M8-style, 8 Channel, 24Vdc Configurable I/O Module w/DeviceLogix	YES	N/R
1738-8CFGM12		M12-style, 8 Channel, 24Vdc Configurable I/O Module	YES	N/R
1738-8CFGM23		M23-style, 8 Channel, 24Vdc Configurable I/O Module	YES	N/R
1738-8CFGM8		M8-style, 8 Channel, 24Vdc Configurable I/O Module	YES	N/R
1738-ACNR		Redundant ControlNet Adapter	YES	N/R
1738-ADN12		M12-style, DeviceNet Adapter with DeviceNet pass-thru connector	YES	N/R
1738-ADN18		M18-style, DeviceNet Adapter with DeviceNet pass-thru connector	YES	N/R
1738-ADN18P		M18-style, DeviceNet Adapter without DeviceNet pass-thru connector	YES	N/R
1738-ADNX		DeviceNet Expansion Adapter	YES	N/R
1738-AENT		EtherNet/IP Adapter	YES	N/R
1738-AENTR		Dual Port EtherNet/IP Adapter	YES	N/R
1738-APB		Profibus Adapter	YES	N/R
1738-EP24DC		24Vdc Voltage Distribution Module	YES	N/R
1738-EXT1		1meter Bus Extension Module	YES	N/R
1738-EXT3		3meter Bus Extension Module	YES	N/R
1738-FPD		Field Power Distribution Module	YES	YES
1738-IA2M12AC3		M12AC3-style, 2 Channel, 120Vac Digital Sinking Input Module	YES	YES
1738-IA2M12AC4		M12AC4-style, 2 Channel, 120Vac Digital Sinking Input Module	YES	YES
1738-IB16DM12		M12-style, 16 Channel, 24Vdc Digital Sinking Diagnostic Input Module	YES	N/R
1738-IB2M12		M12-style, 2 Channel, 24Vdc Digital Sinking Input Module	YES	N/R
1738-IB4DM12		M12-style, 4 Channel, 24Vdc Digital Sinking Diagnostic Input Module	YES	N/R
1738-IB4M12		M12-style, 4 Channel, 24Vdc Digital Sinking Input Module	YES	N/R
1738-IB4M8		M8-style, 4 Channel, 24Vdc Digital Sinking Input Module	YES	N/R
1738-IB8M12		M12-style, 8 Channel, 24Vdc Digital Sinking Input Module	YES	N/R
1738-IB8M23		M23-style, 8 Channel, 24Vdc Digital Sinking Input Module	YES	N/R
1738-IB8M8		M8-style, 8 Channel, 24Vdc Digital Sinking Input Module	YES	N/R
1738-IE2CM12		M12-style, 2 Channel, 20ma Current Analog Input Module	YES	N/R
1738-IE4CM12		M12-style, 4 Channel, 20ma Current Analog Input Module	YES	N/R
1738-IE2VM12		M12-style, 2 Channel, 24Vdc Voltage Analog Input Module	YES	N/R
1738-IJM23		M23-style, 1 Channel, 5Vdc Encoder/Counter Module	YES	N/R
1738-IR2M12		M12-style, 2 Channel, RTD Input Module	YES	N/R
1738-IT2IM12		M12-style, 2 Channel, Isolated Thermocouple Input Module	YES	N/R
1738-IV4M12		M12-style, 4 Channel, 24Vdc Digital Sourcing Input Module	YES	N/R
1738-IV8M12		M12-style, 8 Channel, 24Vdc Digital Sourcing Input Module	YES	N/R
1738-IV8M23		M23-style, 8 Channel, 24Vdc Digital Sourcing Input Module	YES	N/R
1738-IV8M8		M8-style, 8 Channel, 24Vdc Digital Sourcing Input Module	YES	N/R
1738-OA2M12AC3		M12AC3-style, 2 Channel, 240Vac Digital Sourcing Output Module	YES	YES
1738-OB16E19M23		M23-style, 16 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB16E25DS		DB25-style, 16 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB16EM12		M12-style, 16 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB2EM12		M12-style, 2 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB2EPM12		M12-style, 2 Channel, Protected 24Vdc Digital Sourcing Output Mdl.	YES	N/R

¹ Products of the series level shown, or higher, are certified to the directives noted. If no series number is given, then all series are covered.

² YES = Product is certified to this directive.

N/R = This directive is not required for this product (falls below applicable voltage levels).

Catalogue number	Series ¹	Description	Directive ²	
			EMC	LVD
1738-OB4EM12		M12-style, 4 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB4EM8		M8-style, 4 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB8EM12		M12-style, 8 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB8EM23		M23-style, 8 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OB8EM8		M8-style, 8 Channel, 24Vdc Digital Sourcing Output Module	YES	N/R
1738-OE2CM12		M12-style, 2 Channel, 20ma Current Analog Output Module	YES	N/R
1738-OE4CM12		M12-style, 4 Channel, 20ma Current Analog Output Module	YES	N/R
1738-OE2VM12		M12-style, 2 Channel, 24Vdc Voltage Analog Output Module	YES	N/R
1738-OV4EM12		M12-style, 4 Channel, 24Vdc Digital Sinking Output Module	YES	N/R
1738-OW2M12		M12-style, 2 Channel, 24Vdc Relay Module	YES	N/R
1738-OW4M12		M12-style, 4 Channel, 24Vdc Relay Module	YES	N/R
1738-OW4M12AC		M12AC-style, 4 Channel, 125Vdc/240Vac Relay Module	YES	YES
1738-SSIM23		M23-style, Synchronous Serial Interface Module	YES	N/R
1738-VHSC24M23		M23-style, 1 Channel, 24Vdc High Speed Counter Module	YES	N/R

¹ Products of the series level shown, or higher, are certified to the directives noted. If no series number is given, then all series are covered.

² YES = Product is certified to this directive.

N/R = This directive is not required for this product (falls below applicable voltage levels).