

**EC Declaration of Conformity**

The undersigned, representing the following supplier

**Rockwell Automation, Inc.**  
1201 South 2<sup>nd</sup> Street  
Milwaukee, WI 53204  
USA

and the authorised representative established within the  
Community

**Rockwell Automation, Division of  
Rockwell International GmbH**  
Düsselberger Str. 15  
D-42781 Haan, Germany

herewith declare that the Products

**IEC Circuit Breakers for Equipment**

Product identification (brand and  
catalogue number/part number):

**Allen-Bradley 1492-GH, -GHA, -GHD, and -GS, followed by  
suffixes**  
(reference the attached list of catalogue numbers)

---

are in conformity with the provisions of the following EC Directive(s) when installed in accordance with the  
installation instructions contained in the product documentation:

73/23/EEC

Low Voltage Directive as amended by 93/68/EEC

---

and that the standards and/or technical specifications referenced below have been applied:

EN 60934:2001

Circuit-breakers for equipment (CBE)

---


Year of CE Marking

1995

---

Supplier:

Authorised Representative in the Community:



**Signature**

Name: Daniel L. Nachtigall  
Position: Supervisor, Standards  
Date: 28-Nov-2006



i.V.

**Signature**

Name: Viktor Schiffer  
Position: Engineering Manager  
Date: 15-Dec-2006

<i>Catalogue number</i>	<i>Series<sup>1</sup></i>	<i>Description</i>
1492-GHx		<i>Single range timing relay per Nomenclature</i>
1492-GHAx		<i>Fixed range timing relay per Nomenclature</i>
1492-GHDx		<i>Single range timing relay per Nomenclature</i>
1492-GSxx		<i>Fixed range timing relay per Nomenclature</i>

1) *If no series number is given, then all series are covered*

**NOMENCLATURE:**

1492	-	GH	160
1		2	3

1	Designates Product Type 1492 – Miniature circuit breaker			
2	Designates Relay Type GH – High density, single pole GHA – High density, single pole w/auxiliary GHD – High density, double pole			
3	Designates Current			
	Rating	012 – 1.2 A	030 – 3.0 A	080 – 8.0 A
	002 – 0.2 A	015 – 1.5 A	040 – 4.0 A	100 – 10.0 A
	005 – 0.5 A	020 – 2.0 A	050 – 5.0 A	150 – 15.0 A
	008 – 0.8 A	025 – 2.5 A	070 – 7.0 A	160 – 16.0 A
	010 – 1.0 A			

1492	-	GS	3	G	250	H1
1		2	3	4	5	6

1	Designates Product Type 1492 – Miniature circuit breaker			
2	Designates Relay Type GS – High density, thermal/magnetic			
3	Designates Number of Poles 1 – 1 pole 2 – 2 pole 3 – 3 pole			
4	Designates Trip Characteristic G – All devices are so rated			
5	Designates Current			
	Rating	020 – 2.0 A	060 – 6.0 A	150 – 15.0 A
	002 – 0.2 A	025 – 2.5 A	070 – 7.0 A	160 – 16.0 A
	005 – 0.5 A	030 – 3.0 A	080 – 8.0 A	200 – 20.0 A
	008 – 0.8 A	040 – 4.0 A	100 – 10.0 A	250 – 25.0 A
	010 – 1.0 A	050 – 5.0 A	120 – 12.0 A	
	015 – 1.5 A			
6	Designates Options H1 – N.O. auxiliary contacts H2 – N.C. auxiliary contacts			