

EC Declaration of Conformity

The undersigned, representing the supplier
Rockwell Automation, Inc.
1201 South 2nd Street
Milwaukee, WI 53204
U.S.A.

and the authorised representative within the Community
Rockwell Automation European Headquarters SA/NV
Vorstlaan/Boulevard du Souverain 36 – BP 3A/B
B-1170 Brussels
Belgium

herewith declare that the Products ***IEC Miniature Circuit Breakers***

Product identification (brand and catalogue number/part number): ***Allen-Bradley 188 Series***
(reference the attached list of catalogue numbers)

are in conformity with the provisions of the following EC Directive(s) when installed in accordance with the installation instructions contained in the product documentation:


2006/95/EC *Low Voltage Directive*

and that the standards and/or technical specifications referenced below have been applied:


EN 60898-1:2003 + A1:2004 *Electrical accessories – Circuit breakers for overcurrent protection for household and similar installations – Part 1: Circuit breakers for a.c. operation*

Year of CE Marking 2008

Supplier: *Authorised Representative in the Community:*



Signature
Name: Daniel L. Nachtigall
Position: Spv – Product Certification Engineering
Date: 12-Jul-2008



Signature
Name: Viktor Schiffer
Position: Engineering Manager
Date: 16-Jul-2008

<i>Catalogue number</i>	<i>Series¹</i>	<i>Description</i>
188-xxxx-x		<i>IEC miniature circuit breakers per Nomenclature</i>

1) If no series number is given, then all series are covered

MODEL NOMENCLATURE:

188	-	A	3	C	500	-	N
1		2	3	4	5		6

1	Product Line 188 – Miniature circuit breakers																												
2	Designates Short Circuit Current Rating A – 10 kA B – 6 kA																												
3	Designates Number of Poles 1 – 1 pole 2 – 2 pole 3 – 3 pole 4 – 4 pole																												
4	Designates Trip Curve B – Trip curve B C – Trip curve C D – Trip curve D																												
5	Designates Current Rating <table style="width: 100%; border: none;"> <tbody> <tr> <td>0016 – .016 A</td> <td>020 – 2.0 A</td> <td>080 – 8.0 A</td> <td>200 – 20.0 A</td> </tr> <tr> <td>0025 – 0.25 A</td> <td>025 – 2.5 A</td> <td>100 – 10.0 A</td> <td>250 – 25.0 A</td> </tr> <tr> <td>005 – 0.5 A</td> <td>030 – 3.0 A</td> <td>120 – 12.0 A</td> <td>320 – 32.0 A</td> </tr> <tr> <td>0075 – 0.75 A</td> <td>035 – 3.5 A</td> <td>130 – 13.0 A</td> <td>400 – 40.0 A</td> </tr> <tr> <td>010 – 01.0 A</td> <td>040 – 4.0 A</td> <td>140 – 14.0 A</td> <td>500 – 50.0 A</td> </tr> <tr> <td>015 – 1.5 A</td> <td>050 – 5.0 A</td> <td>150 – 15.0 A</td> <td>630 – 63.0 A</td> </tr> <tr> <td>016 – 1.6 A</td> <td>060 – 6.0 A</td> <td>160 – 16.0 A</td> <td></td> </tr> </tbody> </table>	0016 – .016 A	020 – 2.0 A	080 – 8.0 A	200 – 20.0 A	0025 – 0.25 A	025 – 2.5 A	100 – 10.0 A	250 – 25.0 A	005 – 0.5 A	030 – 3.0 A	120 – 12.0 A	320 – 32.0 A	0075 – 0.75 A	035 – 3.5 A	130 – 13.0 A	400 – 40.0 A	010 – 01.0 A	040 – 4.0 A	140 – 14.0 A	500 – 50.0 A	015 – 1.5 A	050 – 5.0 A	150 – 15.0 A	630 – 63.0 A	016 – 1.6 A	060 – 6.0 A	160 – 16.0 A	
0016 – .016 A	020 – 2.0 A	080 – 8.0 A	200 – 20.0 A																										
0025 – 0.25 A	025 – 2.5 A	100 – 10.0 A	250 – 25.0 A																										
005 – 0.5 A	030 – 3.0 A	120 – 12.0 A	320 – 32.0 A																										
0075 – 0.75 A	035 – 3.5 A	130 – 13.0 A	400 – 40.0 A																										
010 – 01.0 A	040 – 4.0 A	140 – 14.0 A	500 – 50.0 A																										
015 – 1.5 A	050 – 5.0 A	150 – 15.0 A	630 – 63.0 A																										
016 – 1.6 A	060 – 6.0 A	160 – 16.0 A																											
6	Designates Neutral Pole Blank – No neutral pole N – Neutral pole provided																												