

TX7000™ Shielded Marine Copper Cable – S/FTP

specifications

Category 7 cable shall meet or exceed the IEC 61156-5 Category 7 component standard and be characterized to 1000 MHz. The conductors shall be stranded copper wire construction with polyethylene insulation. The copper conductors shall be twisted in pairs each surrounded by a foil, covered with an overall braided shield within an oil and fuel resistant, halogen-free, fire retardant LSHF-FR jacket.



technical information

Electrical performance:	Certified channel performance in a 4-connector configuration up to 100 meters and exceeds the requirements of ISO 11801 Class E _A and ANSI/TIA-568-C.2 Category 6A standards for supporting 10GBASE-T transmission over twisted-pair cabling systems as part of the Panduit® TX6A™ 10Gig™ Shielded Copper Cabling System Certified component performance up to 100 meters and meets or exceeds the component requirement of the IEC 61156-5 Category 7 standard at swept frequencies up to 600 MHz
Conductors/insulators:	Stranded copper wire insulated with polyethylene
Standards:	EN 50173-1, EN 50288-4-1, ISO/IEC 11801, IEC 61156-5, DNV specification number 6-827.50-2, IEC 60092-360
Certifications:	DNV certification number E-10447, ABS certification number 10-HS638424-1-PDA
Flame rating:	IEC 60754-1, IEC 60754-2, IEC 61034-2, IEC 60332-3-24
PoE compliance:	Meets IEEE 802.3af and IEEE 802.3at for PoE applications
Chemical resistance:	Mineral oil IRM 902 (IEC 60811-2-1) 7 days/23°C (73°F); 4 hours/70°C (158°F) Diesel fuel IRM 903 (IEC 60811-2-1) 7 days/23°C (73°F); 4 hours/70°C (158°F)
Installation tension:	100 N maximum (22 lbf)
Temperature rating:	-15°C to 50°C during installation (5°F to 122°F) -40°C to 85°C during operation (-40°F to 185°F)
Cable jacket:	Oil and fuel resistant, halogen free and fire retardant jacket LSHF-FR, (SHF1)
Cable diameter:	7.9mm (0.314 in.) nominal
Cable weight:	38 kg/500 m (84 lbs./500 m)
Packaging:	500 or 1000 meters (1640 or 3280 feet) on a reel Package tested to ISTA procedure 1A or 1B

key features and benefits

23 AWG stranded conductor wire	Provides exceptional signal strength and electrical performance for high vibration environments
Individually foiled pairs	Prevents the coupling near-end crosstalk and alien crosstalk between twisted pairs to ensure 10GBASE-T transmission performance
Overall braided shield	Provides superior structural integrity and reduces low frequency external interference to ensure exceptional cable performance
Robust jacketing	Oil and fuel resistant for harsh environments
Tested beyond the standards	Cable has been characterized to 1000 MHz, 400 MHz above the standard
Descending length cable markings	Easy identification of remaining cable reduces installation time and cable scrap
Bulk packaging	Supplied in reels for ease of installation
Third party tested	Exceeds the application requirements of Det Norske Veritas, American Bureau of Shipping, and ETL

applications

The TX7000™ Shielded Copper Cable is a component of the TX6A™ 10Gig™ Shielded Copper Cabling System. This end-to-end system provides a cost effective media for ensuring that the most challenging network bandwidth needs are easily met today and tomorrow. The durable, flame and oil resistant jacket used in the TX7000™ S/FTP

Shielded Copper Cable makes it the ideal choice for use in harsh environments encountered in marine applications including ship and offshore/onshore units. The use of shielding in the cable offers superior performance in uncertain high EMI environments for ultimate signal integrity.

www.panduit.com

PANDUIT®

SPECIFICATION SHEET

TX6A™ 10Gig™ Shielded Copper Cabling System

TX7000™ S/FTP Copper Cable

LSHF-FR: PSM7004*

Mini-Com® TX6A™ 10Gig™ Shielded Jack Module

Jack module: CJS6X88TGY

TX6A™ 10Gig™ Shielded CM/LSZH Patch Cords

Feet: STP6X**IG

Meters: STP6X***MIG

Mini-Com® All Metal Shielded Angled Modular Patch Panels

24-port, 1 RU: CPA24BLY

48-port, 2 RU: CPA48BLY

Mini-Com® All Metal Shielded Flat Modular Patch Panels

24-port, 1 RU: CP24BLY

48-port, 2 RU: CP48BLY

72-port, 2 RU: CP72BLY

Cable Prep Tools

Wire

snipping tool: CWST

Wire

stripping tool: CJUST

*Cable color is IG (International Gray) and/or BU (Blue). For other cable colors please contact customer service.

**For lengths 3 to 20 feet (increments of one foot) and 25, 30, 35, 40 feet, change the length designation in the part number to desired length. For standard cable colors other than IG (International Gray) substitute IG suffix with BL (Black), BU (Blue), GR (Green), RD (Red), YL (Yellow), OR (Orange), or VL (Violet) to the end of the part number. For example the part number for a blue, 15-foot patch cord is STP6X15BU.

***For lengths 1 to 10 meters (increments of one meter) and 1.5, 2.5, 15, 20 meters, change the length designation in the part number to the desired length. For standard cable colors other than IG (International Gray) substitute IG suffix with BL (Black), BU (Blue), GR (Green), RD (Red), YL (Yellow), OR (Orange), or VL (Violet) to the end of the part number. For example, the part number for a blue, 15-meter patch cord is STP6X15MBU.


Contact customer service for bulk packaged and/or keyed jack modules and patch cords.

TX7000™ Shielded Marine Copper Cable – S/FTP

additional specifications

Mechanical Test	
Ultimate Breaking Strength	>400 N (90 lbf)
Minimum Bend Radius	8 x cable diameter
Electrical Test	
Nominal Velocity of Propagation (NVP)	76% nominal

cable construction



product offering

Part Number	Packaging Configuration	Reel Size
PSM7004*-KED	Standard Euro Pallet (12 reels/pallet)	500m
PSM7004*-KD	Standard Pallet (12 reels/pallet)	500m
PSM7004*-KM	Standard Pallet (4 reels/pallet)	1000m
PSM7004*-KEM	Standard Euro Pallet (4 reels/pallet)	1000m

*Cable color is IG (International Gray) or BU (Blue). For other cable colors, please contact customer service.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300 and reference COSP182

PANDUIT®

©2012 Panduit Corp.
ALL RIGHTS RESERVED.

WW-COSP182

3/2012